



# CorePro LEDspot MV

## CorePro LEDspotMV ND 2.2-30W 827 R39 36D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Product data


General Information		Lamp current (nom.)	
Cap base	E14 [ E14]		21 mA
Bulb shape	R39 [ R 39mm]	Wattage equivalent	28 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50000X	Warm-up time to 60% light (nom.)	1 s
Technical type	2.2-28W	Power factor (nom.)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Beam Angle (Nom)	36 °	T-Case maximum (nom.)	82 °C
Luminous intensity (nom.)	250 cd		
Colour designation	Warm white (WW)	Controls and Dimming	
Rated beam angle	36 °	Dimmable	No
Correlated colour temperature (nom.)	2700 K		
Luminous efficacy (rated) (nom.)	68.18 lm/W	Approval and Application	
Colour consistency	<6	Energy-saving product	Yes
Color rendering index (nom.)	80	Suitable for accent lighting	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A++
Luminous Flux In 90° Cone (Rated)	150 lm	Energy Consumption kWh/1000 h	3 kWh
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869658404000
Power (Rated) (Nom)	2.2 W	Order product name	CorePro LEDspotMV ND 2.2-30W 827 R39 36D

# CorePro LEDspot MV

EAN/UPC – product	8718696584040
Order code	58404000
Numerator – quantity per pack	1
Numerator – packs per outer box	6

Material no. (12NC)	929001235502
Net weight (piece)	0.030 kg

## Dimensional drawing




Product	D	C
CorePro LEDspotMV ND 2.2-30W 827 R39 36D	39 mm	66 mm

R39 220-240V 3W-25W 150lm 2700K E14 ND

Photometric data

Accent Lighting - Spots



2016-02-16

