



# CorePro LEDspot MV

## CorePro LEDspotMV ND 3.7-60W 827 R80 40D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a E27 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Product data


General Information		Lamp current (nom.)	
Cap base	E27 [ E27]		32 mA
Bulb shape	R80 [ R 80mm]	Wattage equivalent	60 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50000X	Warm-up time to 60% light (nom.)	1 s
Technical type	3.7-60W	Power factor (nom.)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Beam Angle (Nom)	40 °	T-Case maximum (nom.)	67 °C
Luminous intensity (nom.)	850 cd		
Colour designation	Warm white (WW)	Controls and Dimming	
Rated beam angle	40 °	Dimmable	No
Correlated colour temperature (nom.)	2700 K		
Luminous efficacy (rated) (nom.)	100.00 lm/W	Approval and Application	
Colour consistency	<6	Energy-saving product	Yes
Color rendering index (nom.)	80	Suitable for accent lighting	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A++
Luminous Flux In 90° Cone (Rated)	370 lm	Energy Consumption kWh/1000 h	4 kWh
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869658406400
Power (Rated) (Nom)	3.7 W	Order product name	CorePro LEDspotMV ND 3.7-60W 827 R80 40D

## CorePro LEDspot MV

EAN/UPC – product	8718696584064
Order code	58406400
Numerator – quantity per pack	1
Numerator – packs per outer box	6

Material no. (12NC)	929001235602
Net weight (piece)	0.088 kg

### Dimensional drawing




R80 220-240V 6W-60W 345lm 2700K E27 ND

Product	D	C
CorePro LEDspotMV ND 3.7-60W 827 R80 40D	80 mm	113 mm

Photometric data

Accent Lighting - Spots



## CorePro LEDspot MV

