



Classic filament LED Lamps

CLA LEDBulb D 8-60W ST64 E27 827 CL

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Bulb shape	ST64
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	7-60W
Light Technical	
Luminous flux (nom.)	806 lm
Luminous flux (rated) (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	115.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50-60 Hz


Power (Rated) (Nom)	7 W
Lamp current (nom.)	40 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy efficiency label (EEL)	A++

Classic filament LED Lamps

Energy Consumption kWh/1000 h	7 kWh
Product Data	
Full product code	871869657569700
Order product name	CLA LEDBulb D 7-60W ST64 E27 827 CL
EAN/UPC – product	8718696575697
Order code	57569700

Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001228602
Net weight (piece)	0.060 kg

Dimensional drawing



filament 7W-60W 806lm NAD 2700K E27D

Product	D	C
CLA LEDBulb D 7-60W ST64 E27 827 CL	64 mm	148 mm

Photometric data

General Uniform Lighting

