

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

PROPOWER LUBRICANT WD
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylids Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical:	Aerosols, category 1 Extremely flammable aerosol. Pressurised container: May burst if heated.
Health:	Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness. Specific Target Organ Toxicity - Repeated Exposure Category 1 Causes damage to organs through prolonged or repeated exposure .
Environment:	Hazardous to the aquatic environment, chronic category 2 Toxic to aquatic life with long lasting effects.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

Product identifier: Contains:
Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s):
 H222 : Extremely flammable aerosol.
 H229 : Pressurised container: May burst if heated.
 H336 : May cause drowsiness or dizziness.
 H372 : Causes damage to organs through prolonged or repeated exposure .
 H411 : Toxic to aquatic life with long lasting effects.

Precautionary statement(s):
 P102 : Keep out of reach of children.
 P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P211 : Do not spray on an open flame or other ignition source.
 P251 : Do not pierce or burn, even after use.
 P260 : Do not breathe dust/fume/gas/mist/vapours/spray.
 P271 : Use only outdoors or in a well-ventilated area.
 P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 P501-2 : Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information: Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic	01-2119458049-33	-	919-446-0	30-60	Flam. Liq. 3, Asp. Tox. 1, STOT SE 3, STOT RE 1, Aquatic Chronic 2	H226,H304,H336,H372,H411	B
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	10-30	Press. Gas, Flam. Gas 1	H280,H220	K,G

Explanation notes

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water If eye irritation persists: Get medical advice/attention.
Contact with skin :	Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Anti Corrosion Products

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

No information available

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
hands and skin :	Wear suitable protective gloves
Recommended gloves:	Nitrile
eyes :	Wear safety goggles according to EN 166.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state :	Propane/butane propelled liquid.
colour :	Amber.
odour :	Characteristic odor.
pH :	Not applicable.
Boiling point/range :	150 °C
Flash point :	38 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	9.4 %
lower limit :	0.9 %
Vapour pressure :	Not available.
Relative density :	0.805 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	230 °C
Viscosity :	Not available.

9.2. Other information

VOC: 601 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis Repeated exposure may cause skin dryness or cracking.
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic	-	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 10 mg/l
		LD50 derm.rabit	> 4 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2
 Toxic to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

Hydrocarbons, C9-12, n-alkanes, isoalkanes, cyclic	-	IC50 algae	4.6-10 mg/l
		LC50 fish	10-30 mg/l
		EC50 daphnia	10-22 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

GWP (global warming potential): 0

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS (hydrocarbons)

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes
IMDG - Marine pollutant: Marine pollutant
IATA/ICAO - Environmentally hazardous: Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R10: Flammable.
R12: Extremely flammable.
R65: Harmful: may cause lung damage if swallowed.
R67: Vapours may cause drowsiness and dizziness.
R48/23/24/24
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

*Explanation hazard statements: H220 : Extremely flammable gas.
H226 : Flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H336 : May cause drowsiness or dizziness.

Productname : PROPOWER LUBRICANT WD
Ref.Nr.: UDS000684_3_20160729 (EN)

Creationdate : 29.07.16 Version : 1.0
Replaces: UDS000684_20150324

H372 : Causes damage to organs through prolonged or repeated exposure .

H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.