


Tantalum, MnO₂ Tantalum, Commercial Grade, T350, 10 uF, 10%, 25 V, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 2.54mm



Dimensions

D	5.5mm
H	8.9mm
S	2.54mm +/-0.38mm
LL	12.7mm +/-1.26mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	1000

General Information

Dielectric:	MnO ₂ Tantalum
Style:	Radial
Series:	T350
Description:	Radial, Solid Tantalum, Conformal, Dipped
Features:	Low Leakage
RoHS:	Yes
Termination:	Tin
Notes:	Longest Lead Is Positive

Specifications

Capacitance:	10 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC (85C), 21 VDC (125C Surge), 0.25 V (125C Reverse)
Temperature Range:	-55/+125C
Dissipation Factor:	6%
Leakage:	2 uAmps