


Tantalum, MnO₂ Tantalum, Commercial Grade, T350, 22 uF, 10%, 16 V, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 2.54mm



Dimensions

D	6mm
H	9.9mm
S	2.54mm +/-0.38mm
LL	12.7mm +/-1.26mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	50

General Information

Dielectric:	MnO ₂ Tantalum
Style:	Radial
Series:	T350
Description:	Radial, Solid Tantalum, Conformal, Dipped
Features:	Low Leakage
RoHS:	Yes
Termination:	Tin
Notes:	Longest Lead Is Positive

Specifications

Capacitance:	22 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC (85C), 12 VDC (125C Surge), 0.16 V (125C Reverse)
Temperature Range:	-55/+125C
Dissipation Factor:	6%
Leakage:	2.6 uAmps