

## LEDVANCE® Damp Proof

### LED damp-proof luminaire



#### Area of application

- Ideal for industrial and storage facilities
- Car parks and underpasses
- Garages
- Workshops, assembly lines


#### Product benefits

- Homogeneous light with wide beam angle
- Energy savings of up to 50% (compared to luminaires that use fluorescent lamps)
- Through-wiring possible
- No EMC risk thanks to LED module integrated in luminaire cover
- Easy installation, no tools required for connection
- Stainless steel clamps with safety screws
- All mounting accessories included (suspension kit, theft protection kit)
- Available certificates: CE, CB, TUEV SUED

#### Product features

- Luminaire efficacy: 115 lm/W
- Luminous flux: up to 6400lm
- Available with color temperature: 4000K, 6500K
- Beam angle: 180°
- Type of protection: IP65
- Polycarbonate grey housing, Polycarbonate transparent diffuser
- Ambient operating temperature: -30...+50 °C
- Lifetime (L70/B50): up to 50000h
- 5-Years guarantee

## Technical data



Product description	GTIN (EAN)	Nominal wattage [W]	Nominal voltage [V]	Power factor [λ]	Luminous flux [lm]	Luminaire efficacy [lm/W]	Colour temperature [K]	CRI index [Ra]
DampProofLED 1200 39W/6500K IP65	4058075000865	39W	230V	> 0.9	4400	115	6500K	>80
DampProofLED 1500 55W/6500K IP65	4058075000889	55W	230V	> 0.9	6400	115	6500K	>80
DampProofLED 1200 21W/4000K IP65	4058075000902	21W	230V	> 0.9	2400	115	4000K	>80
DampProofLED 1200 39W/4000K IP65	4058075000926	39W	230V	> 0.9	4400	115	4000K	>80
DampProofLED 1500 30W/4000K IP65	4058075000940	30W	230V	> 0.9	3500	115	4000K	>80
DampProofLED 1500 55W/4000K IP65	4058075000964	55W	230V	> 0.9	6400	115	4000K	>80

Product description	Beam angle	Rated life time L70 / B50 [h]	Type of protection IP rating	Protection class	Product size l x w or Ø [mm]	Height h [mm]	Body colour
DampProofLED 1200 39W/6500K IP65	n/a	50000	65	I	1200 x 95	78	grey
DampProofLED 1500 55W/6500K IP65	n/a	50000	65	I	1500 x 95	78	grey
DampProofLED 1200 21W/4000K IP65	n/a	50000	65	I	1200 x 95	78	grey
DampProofLED 1200 39W/4000K IP65	n/a	50000	65	I	1200 x 95	78	grey
DampProofLED 1500 30W/4000K IP65	n/a	50000	65	I	1500 x 95	78	grey
DampProofLED 1500 55W/4000K IP65	n/a	50000	65	I	1500 x 95	78	grey

## Packaging information

Product description	GTIN (EAN)	Dimensions EAN10 l x w x h [mm]	Gross weight EAN 10 [g]	Volume [dm³]	Packaging unit [Pieces/unit]
DampProofLED 1200 21W/4000K IP65	4058075000902	1205 x 102 x 84	1999	13.05	6
DampProofLED 1200 39W/4000K IP65	4058075000926	1205 x 102 x 84	1999	13.05	6
DampProofLED 1200 39W/6500K IP65	4058075000865	1205 x 102 x 84	1999	13.05	6
DampProofLED 1500 30W/4000K IP65	4058075000940	1505 x 102 x 84	2726	16.25	6
DampProofLED 1500 55W/4000K IP65	4058075000964	1505 x 102 x 84	2726	16.25	6
DampProofLED 1500 55W/6500K IP65	4058075000889	1505 x 102 x 84	2726	16.25	6

## Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.