

KEMET Part Number: C410C223K5R5TA7200
(C410C223K5R5TATR)

Ceramic, Commercial Grade, AxiMax, 0.022 uF, 10%, 50 V, X7R



Dimensions	
D	2.31mm MAX
L	4.32mm MAX
LL	25.4mm +0.025/-0.076mm
F	0.51mm +0.025/-0.076mm

Packaging Specifications	
Packaging:	T&R, 305mm
Packaging Quantity:	5000

General Information	
Series:	AxiMax
Description:	AxiMax, Commercial Standard
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A

Specifications	
Capacitance:	0.022 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	45.45 GOhms
Dielectric Strength:	125 V