
KEMET Part Number: EE2-12NUH-L

(USREE21200NUHL, EE212NUHL)

Relays, Signal, EE2



Dimensions			
L	15mm MAX		
W	7.5mm MAX		
Н	10mm MAX		
LL	1mm +/-0.1mm		
S	5.08mm +/-0.2mm		
\$1	2.54mm +/-0.2mm		
F	1mm +/-0.1mm		
F1	2mm +/-0.1mm		

Packaging Specifications		
Packaging:	T&R	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2017 IntelliData.net

General Information			
Style:	SMD		
Series:	EE2		
Description:	Miniature Signal Relay, Non-latch		
Features:	Compact and light weight. FCC (1500 V) and Telcordia (2500 V) surge capacity. UL recognized and CSA certified. Low power consumption (100-200 mW). ND type (High insulation). NKX type (High breakdown voltage) can withstand 1.5KVAC at open contacts.		
RoHS:	Yes		

Coil Type:

Single Coil (Non-Latching)

Specifications			
Specifications			
Temperature Range:	-40/+85C		
Coil Voltage:	12 V		
Coil Resistance:	1028 Ohms +/-10%		
Contact Form:	2 Form C (DPDT)		
Contact Material:	Silver Alloy With Gold Alloy Overlay		
Voltage Characteristics:	9 (Operate) / 1.2 (Release)		
Switching Power:	60 W, 125 VA		
Switching Voltage DC:	220 V		
Switching Voltage AC:	250 VAC		
Switching Current:	2 Amps		
Contact Current Class:	>10A		
Carrying Current:	2 Amps		
Contact Resistance:	75 mOhms		
Operation Time:	Approximately 2ms		
Release Time:	Approximately 1ms		
Insulation Resistance:	1 GOhms		
Withstanding Voltage:	1000 VAC (1min) 1500 V Surge		

