# **Data Sheet**




# SUCOTEST\_18A\_Stock Assembly

## **Description**

Sucotest 18A armoured test assemblies offer excellent electrical performance (low insertion loss combined with unique stability and excellent return loss) for heavy duty, outdoor and harsh environment measurements up to 18 GHz.

Product description Item number ST18A/Nm/Nm/1500mm

84013029



# **Product Configuration**

Cable type SUCOTEST\_18A

Ruggedisation Steel wire spring, steel braid, TPU jacket blue

Length of assembly1'500 mmConnector AN straight maleConnector BN straight male

### **Technical Data**

#### **Mechanical Data**

Diameter: 10.3 mm
Min. bending radius static 30 mm
Min. bending radius repeated 50 mm
Recommended mating torque (\*) 1.0 Nm
Waterproof IP 68

Flex life 100'000 cycles

Weight 300 g

#### **Environmental Data**

 $\begin{array}{lll} \text{Operating temperature} & -40^{\circ}\text{C to} + 85^{\circ}\text{C} \\ \text{Storage temperature} & -40^{\circ}\text{C to} + 85^{\circ}\text{C} \\ \text{RoHS, REACH} & \text{Compliant} \end{array}$ 

#### **Electrical Data**

Return Loss min. 19.0 dB (up to 18 GHz)
Insertion loss (assembly) max. 2.74 dB (18 GHz, 25°C)
Power handling min. 120 W (18 GHz, sea level

Power handling min. 120 W (18 GHz, sea level, 25°C) Screening effectiveness > 90 dB (up to 18 GHz)

Insertion loss stability vs. bending (\*\*) +/- 0.2 dB (up to 18 GHz) Phase stability vs. bending (\*\*)  $< 0.7^{\circ}$  (el/GHz)

#### **General Information**

(\*) H+S torque wrench H+S description: 74\_Z-0-0-193 // material/item number: 22645085

(\*\*) Stability test 360°, diameter 55 mm

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.