






REVISIONS				
RevNo	Description	Date	REVISION	Mender
1				
2				



- 1.MATERIALS:
a BODY:ZINC ALLOY,DIE CASTIN NICKEL PLATED.
b CONTACT:BRASS NICKEL PLATED.
c BRACKET:A.B.S UL 94VO.
d INSULATOR:ENGINEER PLASTIC POM UL 94HB.
2.NORMAL IMPEDENCE 50(75)OHMS.
3.FREQUENCY RANGE:0-2 GHZ.
4.MAX PEAK VOLTAGE:500V.
5.DIELECTRIC STRENGTH WITHSTAND 1.5KV RMS FOR ONE MINUTE.
6.INSULATION RESISTANCE AT 500VDE 5000 MEGOHMS MAL.



PCB LAYOUT

6	SHEET COPPER	BRASS	1	NICKEL PLATED
5	CENTER CONTACT	BRASS	2	NICKEL PLATED
4	CENTER CONTACT	BRASS	2	NICKEL PLATED
3	INSULATOR	POM	2	NATURAL
2	BODY	ZINC	2	NICKEL PLATED
1	HOUSING	ABS UL 94V0	1	BLACK
ITEM	DESCRIPTION	MATERIAL	Q'TY	FINISHED

 YIN SHENG COMPANY LTD (ZHONG SHAN)				TITLE TWO BNC FEMALE IN ONE ROW, 90°		
	XXX	UNITS	MM	UNLESS OTHERWISE SPECIFIED TOLERANCES: 0.5-15 = ±0.15 ANGLES 15-30 = ±0.30 ±3° 30-120 = ±0.60 >120 = ±1.00	DESIGNED	Zs
PART NO.		SCALE	FIT		DRAWING	Zs
MODEL NO.	SB124(1X2)-VO				CHECKED	David
DRAWING NO.		EDITION	A1		APPROVED	Andy
CAD FILE	Yin sheng/Yifaxing/sb/sb124			2005/06/23	 3RD ANGLE	