

# LCD COLOUR MONITOR



## Model No. L156HDL

15.6" TFT LCD Full HD Colour Wide Screen Monitor 1920 x 1080P with LED Back Light, inputs of HDMI, DVI, VGA, 2 x Composite video In/Out BNC, Y/C (S-Video) in. Audio In/Out and via Speakers, I/R Remote Control.

**Options:** 19" Rack Mount, Touch screen, Glass front. Other sizes available.



19" Rack Mount option



### Main Features:

- Resolution: 1920 x 1080P – Full HD
- Picture Ratio: 16:9
- Brightness: 300 cd/m2. - LED Back light.
- Contrast Ratio: 600:1
- Inputs: HDMI, DVI, VGA, 2 Composite Video, S-Video, Audio.
- Outputs: 2 x Composite Video BNC, Audio.
- PIP/POP Function VGA/Video
- Mounting: VESA 75 or 100, Key Hole, Stand.
- Slim Aluminium cabinet in Black.
- 3D De-Interlaced Technology.
- Anti-blur/image auto.
- Speaker: 2 Watts max.
- USB Socket: Media and Service use.

The L156HDL with Full HD TFT technology and LED back Light offers Professional sharp images and with high contrast ratio gives superb pictures. With BNC Connectors, Video Loop through, Audio In/Out via speakers this is a truly versatile Monitor. Various mounting options and all finished in a Smart tough Slim style Aluminium Metal housing. This compact unit is ideal for Multimedia Video and Surveillance systems applications.

### SPECIFICATIONS:

- Active area: 344.2 x 193.5 (WxH)mm. • 16.7M Colours. • PAL and NTSC Auto.
- Response Time: 6/2 ms (Tr/Tf). • Viewing angle: Left/Right: 70°, Up/ Down 60°.
- Controls/Indicators: Front: On LED, I/R sensor. Rear: Source, Menu, Item, Up, Down, Power.
- Power Source: 12V DC, 1.1 Amp, 13 Watts approx. AC Adaptor: 90-264 Vac 50/60Hz 1.5Amps.
- Dimensions: 383 x 231 x 47 (62 with stand). Carton: 445 x 390 x 145 (WxHxD)mm.
- Weight: Unit: 3.4 Kgms, Carton: 4.37 Kgms. • Temp: Operation: 0°C~40°C, Storage: -20~ 60°.

**Connections:** Full HD: HDMI Socket. VGA: 15 pin Sub-D. DVI: DVI-D socket. Composite Video In/Out 1 and 2: BNC socket. Y/C (S-Video) Input: 4 pin mini din socket. Audio In/Out 1 and 2: Right and Left Phono sockets. PC Audio in: 3.5mm Jack socket. DC input: 2.1mm socket. AC adaptor: IEC socket. USB: For Media and service use only.

**Standard accessories:** AC adapter, AC Mains Lead, I/R Remote Control.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

## Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29