

SDA3 - 20 - 25 - 30

DIN rail 20, 25 & 30A solid-state contactors

DURAKOOL



- High load voltage - up to 480VAC
- 4 ~ 32VDC or 90 ~ 250VAC control voltage
- Three Phase, Zero cross-over switching
- LED control input indicator
- Integrated heatsink
- RoHS Compliant



Output (load)

Load type	3PST-NO (3 N/O) Resistive	
Load current	20A, 25A, 30A	
Load switching voltage	AC V_{ms}	40 - 480V
Maximum peak voltage	AC V_{pk}	900V
Minimum load current	0.1A	
Inrush Current (max.)	10ms	20A: 240A / 25A: 300A / 30A: 380A
I^2t	20A: 288A ² s / 25A: 450A ² s / 30A: 660A ² s	
Switch type	Zero Cross (Consult factory for Random)	
On voltage drop	V AC	1.6V
Leakage current off	mA	$\leq 10\text{mA}$

Input (control)

Control voltage (rated)	V	DC Control: 4 - 32VDC / AC Control: 90 - 250VAC
Control current	mA	< 20mA
Turn-on voltage (min)	V_{min}	DC Control: 3.5VDC / AC Control: 80VAC
Turn-on voltage (max)	V_{max}	DC Control: 35VDC / AC Control: 280VAC
Turn-off voltage	V	DC Control: 2VDC / AC Control: 40VAC

Insulation

Insulation resistance	$\leq 500\text{M}\Omega$ at 500VDC, 50%RH	
Dielectric strength	V AC	$\geq 2500\text{V}$

General Data

Operating time (typical)	mS	Approximately 1/2 cycle of load frequency + $\leq 1\text{ms}$
Release time (typical)	mS	Approximately 1/2 cycle of load frequency + $\leq 1\text{ms}$
Dimensions	L x W x H	100 x 110 x 130mm
Weight	approx. 982g	
Ambient temperature	storage	-30 to 100°C (No icing or condensation)
	operating	-30 to 80°C (with derating). (No icing or condensation)
Relative Humidity	45 - 85% RH	

SDA3 - 20 - 25 - 30

DIN rail 20, 25 & 30A solid-state contactors

DURAKOOL

