


Aluminum Electrolytic, 85C, ELH, 1500 uF, 20%, 200 V, -25/+85C



#### Dimensions

D	35mm +/-1mm
L	40mm +/-2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	2mm +/-0.1mm

#### Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	200

#### General Information

Dielectric:	Aluminum Electrolytic
Series:	ELH
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin

#### Specifications

Capacitance:	1500 uF
Capacitance Tolerance:	20%
Voltage DC:	200 VDC, 250 VDC (Surge)
Temperature Range:	-25/+85C
Rated Temperature:	85C
Life:	2000 Hrs
Dissipation Factor:	15%
Resistance:	72 mOhms (20kHz 25C)
Current:	3800 mAmps (120Hz)
Leakage:	3000 uAmps (5min 20C)