

KEMET Part Number: T491B475K020AT
(B45196H4475K209)

Tantalum, MnO₂ Tantalum, T491, 4.7 uF, 10%, 20 V, 3528, SMD, MnO₂, Molded, 3 Ohms, 2.1mm



| General Information | |
|---------------------|--------------------------------|
| Dielectric: | MnO ₂ Tantalum |
| Style: | SMD Chip |
| Series: | T491 |
| Description: | SMD, MnO ₂ , Molded |
| RoHS: | Yes |
| Termination: | Tin |

| Specifications | |
|------------------------|---|
| Capacitance: | 4.7 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 20 VDC (85C), 13.4 VDC (125C) |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 6% |
| Failure Rate: | N/A |
| Resistance: | 3 Ohms (100kHz) |
| Current: | 168 mAmps (25C), 151.2 mAmps (85C), 67.2 mAmps (125C) |
| Leakage: | 0.9 uAmps |

| Dimensions | |
|------------|-------------------|
| Footprint | 3528 |
| L | 3.5mm +/-0.2mm |
| W | 2.8mm +/-0.2mm |
| H | 1.9mm +/-0.2mm |
| T | 0.13mm REF |
| S | 0.8mm +0.2/-0.3mm |
| F | 2.2mm +/-0.1mm |
| A | 1.9mm MIN |
| B | 0.4mm +/-0.15mm |
| E | 2.2mm REF |
| G | 1.8mm REF |
| P | 0.5mm REF |
| R | 1mm REF |
| X | 0.1mm +/-0.1mm |

| Packaging Specifications | |
|--------------------------|------------|
| Weight: | 107.45 mg |
| Packaging: | T&R, 178mm |
| Packaging Quantity: | 2000 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.