

KEMET Part Number: C0603H562J3GACTU
(C0603H562J3GAC7867)

Ceramic, 200C, 200C-(CxxxxH), 5600 pF, 5%, 25 V, 0603, COG, SMD, MLCC, High Temperature, Ultra-Stable, Low Loss



General Information	
Style:	SMD Chip
Series:	200C-(CxxxxH)
Chip Size:	0603
Description:	SMD, MLCC, High Temperature, Ultra-Stable, Low Loss
Features:	High Temp, Ultra-Stable, Low Loss
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A

Dimensions	
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
T	0.8mm +/-0.07mm
S	0.7mm MIN
B	0.35mm +/-0.15mm

Packaging Specifications	
Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

Specifications	
Capacitance:	5600 pF
Capacitance Tolerance:	5%
Voltage DC:	25 VDC
Temperature Range:	-55/+200C
Temperature Coefficient:	COG
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms
Dielectric Strength:	62.5 V