

KEMET Part Number: T491C106M020AT
(B45196H4106M309)

Tantalum, MnO₂ Tantalum, T491, 10 uF, 20%, 20 V, 6032, SMD, MnO₂, Molded, 1.6 Ohms, 2.8mm



General Information	
Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO ₂ , Molded
RoHS:	Yes
Termination:	Tin

Specifications	
Capacitance:	10 uF
Capacitance Tolerance:	20%
Voltage DC:	20 VDC (85C), 13.4 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6%
Failure Rate:	N/A
Resistance:	1.6 Ohms (100kHz)
Current:	247 mAmps (25C), 222.3 mAmps (85C), 98.8 mAmps (125C)
Leakage:	2 uAmps

Dimensions	
Footprint	6032
L	6mm +/-0.3mm
W	3.2mm +/-0.3mm
H	2.5mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.2mm +/-0.1mm
A	2.9mm MIN
B	0.5mm +/-0.15mm
E	2.4mm REF
G	2.8mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications	
Weight:	224.48 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.