

**KEMET Part Number: CBR05C220JAGAC**  
(CBR05C220JAGACTU)

Ceramic, High Q, Microwave (CBR), 22 pF, 5%, 250 V, 0505, COG, SMD, Fixed, RF, Ultra High Q, Low ESR, Class I



**Dimensions**

<b>L</b>	1.4mm +0.38/-0.25mm
<b>W</b>	1.4mm +/-0.38mm
<b>T</b>	1.15mm +/-0.15mm
<b>B</b>	0.25mm +0.25/-0.13mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	3000

**General Information**

<b>Style:</b>	SMD Chip
<b>Series:</b>	Microwave (CBR)
<b>Chip Size:</b>	0505
<b>Description:</b>	SMD, Fixed, RF, Ultra High Q, Low ESR, Class I
<b>Features:</b>	Ultra High Q, Low ESR, Class I
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Minimum Q = 1240
<b>Notes:</b>	Solder Reflow Only

**Specifications**

<b>Capacitance:</b>	22 pF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	250 VDC
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	COG
<b>Aging Rate:</b>	0% Loss/Decade Hour
<b>Insulation Resistance:</b>	10 GOhms
<b>Dielectric Strength:</b>	500 V
<b>Quality Factor:</b>	1240