


Film, Metallized Paper, Resistor/Capacitor, P409, 0.22 uF, 20%, 630 V, 85C, Lead Spacing = 20.3mm



General Information	
<b>Dielectric:</b>	Metallized Paper
<b>Style:</b>	Radial
<b>Series:</b>	P409
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Approvals:</b>	ENEC, UL, cUL
<b>Construction:</b>	Molded
<b>Miscellaneous:</b>	Resistor Tolerance: +/-30%. Resistor= 47 Ohms

Dimensions	
<b>L</b>	24mm MAX
<b>H</b>	16.5mm MAX
<b>T</b>	11.3mm MAX
<b>S</b>	20.3mm +/-0.4mm
<b>LL</b>	30mm +5mm
<b>F</b>	0.8mm +/-0.05mm

Specifications	
<b>Capacitance:</b>	0.22 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	630 VDC
<b>Voltage AC:</b>	275 VAC
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	85C
<b>Insulation Resistance:</b>	3 GOhms
<b>Safety Class:</b>	X2

Packaging Specifications	
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	150