

Aluminum Electrolytic, 105C, PEH532, 470 uF, 20%, 200 V, -40/+105C



Dimensions	
D	25mm +1mm
L	35mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Weight:	24 g
Packaging:	Bulk
Packaging Quantity:	100

General Information	
Dielectric:	Aluminum Electrolytic
Series:	PEH532
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
Notes:	Add 0.5mm To D And 1mm To L For Sleeving

Specifications	
Capacitance:	470 uF
Capacitance Tolerance:	20%
Voltage DC:	200 VDC
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	1500 Hrs (Rated Voltage And Ripple Current At 105C), 2000 Hrs (Rated Voltage At 105C)
Resistance:	300 mOhms (100Hz 20C), 170 mOhms (100kHz 20C)
Current:	1.1 Amps (100Hz 105C), 3.1 Amps (20kHz 40C)
Leakage:	282 uAmps (5min 20C)