


KEMET Part Number: PEH532RDG4180M2



Aluminum Electrolytic, 105C, PEH532, 1800 uF, 20%, 200 V, -40/+105C



Dimensions

D	35mm +1mm
L	50mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications

Weight:	72 g
Packaging:	Bulk
Packaging Quantity:	100

General Information

Dielectric:	Aluminum Electrolytic
Series:	PEH532
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
Notes:	Add 0.5mm To D And 1mm To L For Sleeving

Specifications

Capacitance:	1800 uF
Capacitance Tolerance:	20%
Voltage DC:	200 VDC
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	1500 Hrs (Rated Voltage And Ripple Current At 105C), 2000 Hrs (Rated Voltage At 105C)
Resistance:	81 mOhms (100Hz 20C), 45 mOhms (100kHz 20C)
Current:	2.8 Amps (100Hz 105C), 7.7 Amps (20kHz 40C)
Leakage:	1080 uAmps (5min 20C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2017 IntelliData.net