

Film, Metallized Polyester, Commercial Grade, R60, 4.7 uF, 10%, 630 V, 85C, Lead Spacing = 27.5mm



General Information	
<b>Dielectric:</b>	Metallized Polyester
<b>Style:</b>	Radial
<b>Series:</b>	R60
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Miscellaneous:</b>	Upper Operating Temperature Of 125C Is Allowed For A Maximum Operating Time Of 1,000 Hours. Above 85C, DC And AC Voltage Derating Is 1.25%/C.

Dimensions	
<b>L</b>	32mm +0.3mm
<b>H</b>	37mm +1mm
<b>T</b>	22mm +0.2mm
<b>S</b>	27.5mm +/-0.4mm
<b>LL</b>	25mm +2/-1mm
<b>F</b>	0.8mm +/-0.05mm

Specifications	
<b>Capacitance:</b>	4.7 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	630 VDC
<b>Voltage AC:</b>	220 VAC
<b>Temperature Range:</b>	-55/+105C
<b>Rated Temperature:</b>	85C
<b>Dissipation Factor:</b>	1% 1kHz
<b>Insulation Resistance:</b>	10 GOhms
<b>Max dVdt:</b>	10 V
<b>Inductance:</b>	18 nH

Packaging Specifications	
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	112

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.