

KEMET Part Number: C0603S331K5RACTU
(C0603S331K5RAC7867)

Ceramic, Floating Electrode, FloatingElectrode-(CxxxxS), 330 pF, 10%, 50 V, 0603, X7R, SMD, MLCC, FE-CAP, Floating Electrode, Temperature Stable



Dimensions

L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
T	0.8mm +/-0.07mm
S	0.7mm MIN
B	0.35mm +/-0.15mm

Packaging Specifications

Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

General Information

Style:	SMD Chip
Series:	FloatingElectrode-(CxxxxS)
Chip Size:	0603
Description:	SMD, MLCC, FE-CAP, Floating Electrode, Temperature Stable
Features:	FE-CAP, Floating Electrode, Temperature Stable
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications

Capacitance:	330 pF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	100 GOhms
Dielectric Strength:	125 V