

**KEMET Part Number: T491B336K006AT**  
(B45196H1336K209)

Tantalum, MnO2 Tantalum, T491, 33 uF, 10%, 6.3 V, 3528, SMD, MnO2, Molded, 2.2 Ohms, 2.1mm



**Dimensions**

Footprint	3528
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
H	1.9mm +/-0.2mm
T	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	2.2mm +/-0.1mm
A	1.9mm MIN
B	0.4mm +/-0.15mm
E	2.2mm REF
G	1.8mm REF
P	0.5mm REF
R	1mm REF
X	0.1mm +/-0.1mm

**Packaging Specifications**

Weight:	107.45 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

**General Information**

Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO2, Molded
RoHS:	Yes
Termination:	Tin

**Specifications**

Capacitance:	33 uF
Capacitance Tolerance:	10%
Voltage DC:	6.3 VDC (85C), 4.22 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6%
Failure Rate:	N/A
Resistance:	2.2 Ohms (100kHz)
Current:	168 mAmps (25C), 151.2 mAmps (85C), 67.2 mAmps (125C)
Leakage:	2.1 uAmps