


KEMET Part Number: T510X337K010ATE035
(B45396R2337K509)

Tantalum, MnO2 Tantalum, Multi-Anode, T510, 330 uF, 10%, 10 V, 7343, SMD, MnO2, Molded, Multiple Anodes, Low ESR, 35 mOhms, 4.3mm



Dimensions

Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	4mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.8mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	1.7mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	430.15 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information

Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Series:	T510
Description:	SMD, MnO2, Molded, Multiple Anodes, Low ESR
Features:	Multiple Anode, Low ESR
RoHS:	Yes
Termination:	Tin

Specifications

Capacitance:	330 uF
Capacitance Tolerance:	10%
Voltage DC:	10 VDC (85C), 7 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6%
Failure Rate:	N/A
Resistance:	35 mOhms (100kHz)
Current:	2777 mAmps (25C), 2499.3 mAmps (85C), 1110.8 mAmps (125C)
Leakage:	33 uAmps