

KEMET Part Number: T491B474K035AT
(B45196E6474K209)

Tantalum, MnO₂ Tantalum, T491, 0.47 uF, 10%, 35 V, 3528, SMD, MnO₂, Molded, 8 Ohms, 2.1mm



Dimensions

Footprint	3528
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
H	1.9mm +/-0.2mm
T	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	2.2mm +/-0.1mm
A	1.9mm MIN
B	0.4mm +/-0.15mm
E	2.2mm REF
G	1.8mm REF
P	0.5mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	107.45 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

General Information

Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO ₂ , Molded
RoHS:	Yes
Termination:	Tin

Specifications

Capacitance:	0.47 uF
Capacitance Tolerance:	10%
Voltage DC:	35 VDC (85C), 23.45 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	4%
Failure Rate:	N/A
Resistance:	8 Ohms (100kHz)
Current:	103 mAmps (25C), 92.7 mAmps (85C), 41.2 mAmps (125C)
Leakage:	0.5 uAmps