

KEMET Part Number: C1206Y103K2RACTU
(C1206Y103K2RAC7800)

Ceramic, Floating Electrode, FloatingFlexTerm-(CxxxxY), 0.01 uF, 10%, 200 V, 1206, X7R, SMD, MLCC, FF-CAP, Floating Electrode



Dimensions

| | |
|----------|------------------|
| L | 3.3mm +/-0.4mm |
| W | 1.6mm +/-0.35mm |
| T | 0.78mm +/-0.20mm |
| B | 0.6mm +/-0.25mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 4000 |

General Information

| | |
|-----------------------|--|
| Style: | SMD Chip |
| Series: | FloatingFlexTerm-(CxxxxY) |
| Chip Size: | 1206 |
| Description: | SMD, MLCC, FF-CAP, Floating Electrode |
| Features: | FF-CAP, Floating Electrode |
| RoHS: | Yes |
| Termination: | Flexible Termination |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |

Specifications

| | |
|---------------------------------|---------------------|
| Capacitance: | 0.01 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 200 VDC |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 2.5% |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |
| Dielectric Strength: | 500 V |