


Ceramic, Safety, C900_V, 4700 pF, 20%, Y5U, Lead Spacing = 10mm



Dimensions

| | |
|-----------|-----------------|
| D | 14mm MAX |
| T | 5mm MAX |
| S | 10mm +/-1mm |
| LL | 18mm +2/-0mm |
| F | 0.55mm +/-0.1mm |

Packaging Specifications

| | |
|----------------------------|--------------------------------------------------|
| Packaging: | Ammo, H0 = 18mm, Component Pitch = 25.4mm +/-2mm |
| Packaging Quantity: | 1000 |

General Information

| | |
|----------------------|-------------|
| Style: | Radial Disc |
| Series: | C900_V |
| RoHS: | Yes |
| Termination: | Tin |
| Failure Rate: | N/A |
| Halogen Free: | Yes |

Specifications

| | |
|---------------------------------|-----------|
| Capacitance: | 4700 pF |
| Capacitance Tolerance: | 20% |
| Temperature Range: | -25/+125C |
| Temperature Coefficient: | Y5U |
| Dissipation Factor: | 2.5% |
| Insulation Resistance: | 10 GOhms |
| Dielectric Strength: | 4,000 V |