


Aluminum Electrolytic, 85C, ALC10, 0.01 F, 20%, 63 V, -40/+85C



**Dimensions**

<b>D</b>	40mm +1mm
<b>L</b>	35mm +/-2mm
<b>S</b>	22.5mm +/-0.1mm
<b>LL</b>	6.3mm +/-1mm
<b>F</b>	2mm +/-0.1mm

**Packaging Specifications**

<b>Weight:</b>	57 g
<b>Sleeving:</b>	Yes
<b>Packaging:</b>	Bulk

**General Information**

<b>Dielectric:</b>	Aluminum Electrolytic
<b>Series:</b>	ALC10
<b>Description:</b>	Snap-In, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Lead:</b>	4 Pin
<b>Notes:</b>	Dimensions D And L Include Sleeving

**Specifications**

<b>Capacitance:</b>	0.01 F
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	63 VDC, 72.45 VDC (Surge)
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	85C
<b>Life:</b>	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage At 85C)
<b>Resistance:</b>	80 mOhms (100Hz 20C), 72 mOhms (10kHz 20C)
<b>Current:</b>	4.58 Amps (100Hz 85C), 4.67 Amps (10kHz 85C)
<b>Leakage:</b>	3780 uAmps (5min 20C)