


Aluminum Electrolytic, 85C, ALS30, 0.01 F, 20%, 63 V, -40/+85C



General Information	
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Series:</b>	ALS30
<b>Description:</b>	Screw Terminal, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Notes:</b>	Dimensions D And L Include Sleevings. MS (MxH) = M8x12

Dimensions	
<b>D</b>	36mm +/-1mm
<b>L</b>	82mm +/-2mm
<b>T</b>	7.14mm +/-0.5mm
<b>S</b>	12.8mm +/-0.5mm
<b>DT</b>	8mm +/-0.5mm
<b>LT</b>	87.5mm +/-1mm
<b>TD</b>	10mm MIN
<b>V</b>	8mm NOM

Specifications	
<b>Capacitance:</b>	0.01 F
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	63 VDC, 72.5 VDC (Surge)
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	85C
<b>Life:</b>	11000 Hrs (Rated Voltage And Ripple Current At 85C), 22000 Hrs (Rated Voltage At 85C)
<b>Resistance:</b>	17 mOhms (100Hz 20C), 14 mOhms (10kHz 20C)
<b>Current:</b>	10.8 Amps (100Hz 85C), 11.9 Amps (10kHz 85C)
<b>Leakage:</b>	3780 uAmps (5min 20C)

Packaging Specifications	
<b>Weight:</b>	115 g
<b>Sleevings:</b>	Yes
<b>Packaging:</b>	Bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.