


Aluminum Electrolytic, 85C, ALS61, 3300 uF, 20%, 550 V, -40/+85C



| Dimensions | |
|------------|-----------------|
| D | 77mm +/-1mm |
| L | 146mm +/-2mm |
| T | 5.5mm +/-0.5mm |
| S | 31.8mm +/-0.5mm |
| DT | 13mm +/-0.5mm |
| LT | 150.5mm +/-1mm |
| TD | 10mm MIN |
| V | 19mm NOM |
| Z | 10mm NOM |

| Packaging Specifications | |
|--------------------------|-------|
| Weight: | 960 g |
| Sleeving: | Yes |
| Packaging: | Bulk |

| General Information | |
|---------------------|--|
| Dielectric: | Aluminum Electrolytic |
| Series: | ALS61 |
| Description: | High Voltage, Screw Terminal, Aluminum Electrolytic |
| Features: | High Voltage |
| RoHS: | Yes |
| Notes: | Dimensions D And L Include Sleeving. MS (MxH) = M12x16 |

| Specifications | |
|------------------------|---|
| Capacitance: | 3300 uF |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 550 VDC, 605 VDC (Surge) |
| Temperature Range: | -40/+85C |
| Rated Temperature: | 85C |
| Life: | 20000 Hrs |
| Resistance: | 93.45 mOhms (100Hz 20C), 82.5 mOhms (10kHz 20C) |
| Current: | 14.6 Amps (100Hz 85C), 20.9 Amps (10kHz 85C) |
| Leakage: | 6000 uAmps (5min 20C) |