

KEMET Part Number: C0603C339C1GACTU
(C0603C339C1GAC7867)

Ceramic, Commercial-(CxxxxC), 3.3 pF, +/-0.25 pF, 100 V, 0603, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I



| General Information | |
|---------------------|--|
| Style: | SMD Chip |
| Series: | Commercial-(CxxxxC) |
| Chip Size: | 0603 |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |

| Dimensions | |
|------------|------------------|
| L | 1.6mm +/-0.15mm |
| W | 0.8mm +/-0.15mm |
| T | 0.8mm +/-0.07mm |
| S | 0.7mm MIN |
| B | 0.35mm +/-0.15mm |

| Packaging Specifications | |
|--------------------------|------------------------|
| Packaging: | T&R, 180mm, Paper Tape |
| Packaging Quantity: | 4000 |

| Specifications | |
|--------------------------|---------------------|
| Capacitance: | 3.3 pF |
| Capacitance Tolerance: | +/-0.25 pF |
| Voltage DC: | 100 VDC |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | C0G |
| Dissipation Factor: | 0.1% |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |
| Dielectric Strength: | 250 V |