

Tantalum, MnO2 Tantalum, High Temperature, T499, 15 uF, 10%, 16 V, 6032, SMD, MnO2, Molded, Hi-Temp, 175C, Auto, AEC-Q200, N/A, 1.8 Ohms, 2.8mm



General Information	
<b>Dielectric:</b>	MnO2 Tantalum
<b>Style:</b>	SMD Chip
<b>Series:</b>	T499
<b>Description:</b>	SMD, MnO2, Molded, Hi-Temp, 175C, Auto, AEC-Q200
<b>Features:</b>	High Temperature, Automotive
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Approvals:</b>	AEC-Q200
<b>AEC-Q200:</b>	Yes

Dimensions	
<b>Footprint</b>	6032
<b>L</b>	6mm +/-0.3mm
<b>W</b>	3.2mm +/-0.3mm
<b>H</b>	2.5mm +/-0.3mm
<b>T</b>	0.13mm REF
<b>S</b>	1.3mm +/-0.3mm
<b>F</b>	2.2mm +/-0.1mm
<b>A</b>	3.1mm MIN
<b>B</b>	0.5mm +/-0.15mm
<b>E</b>	2.4mm REF
<b>G</b>	2.8mm REF
<b>P</b>	0.9mm REF
<b>R</b>	1mm REF
<b>X</b>	0.1mm +/-0.1mm

Specifications	
<b>Capacitance:</b>	15 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	16 VDC (85C), 12.44 VDC (125C), 8 VDC (175C)
<b>Temperature Range:</b>	-55/+175C
<b>Dissipation Factor:</b>	6%
<b>Failure Rate:</b>	N/A
<b>Resistance:</b>	1800 mOhms (100kHz)
<b>Current:</b>	247 mAmps (25C), 222.3 mAmps (85C), 49.4 mAmps (175C)
<b>Leakage:</b>	2.4 uAmps

Packaging Specifications	
<b>Weight:</b>	224.48 mg
<b>Packaging:</b>	T&R, 178mm
<b>Packaging Quantity:</b>	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.