

**KEMET Part Number: C1812X224K1RACTU**  
(C1812X224K1RAC7800)

Ceramic, FlexTerm-(CxxxxX), 0.22 uF, 10%, 100 V, 1812, X7R, SMD, MLCC, FT-CAP, Temperature Stable



**Dimensions**

<b>L</b>	4.5mm +/-0.4mm
<b>W</b>	3.2mm +/-0.3mm
<b>T</b>	1mm +/-0.10mm
<b>B</b>	0.7mm +/-0.35mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	1000

**General Information**

<b>Style:</b>	SMD Chip
<b>Series:</b>	FlexTerm-(CxxxxX)
<b>Chip Size:</b>	1812
<b>Description:</b>	SMD, MLCC, FT-CAP, Temperature Stable
<b>Features:</b>	FT-CAP, Temperature Stable
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>Marking:</b>	No
<b>Failure Rate:</b>	N/A
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours

**Specifications**

<b>Capacitance:</b>	0.22 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	100 VDC
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	X7R
<b>Dissipation Factor:</b>	2.5%
<b>Aging Rate:</b>	3% Loss/Decade Hour
<b>Insulation Resistance:</b>	4.55 GOhms
<b>Dielectric Strength:</b>	250 V