


**KEMET Part Number: C1210Y103K2RACTU**  
(C1210Y103K2RAC7800)

Ceramic, Floating Electrode, FloatingFlexTerm-(CxxxxY), 0.01 uF, 10%, 200 V, 1210, X7R, SMD, MLCC, FF-CAP, Floating Electrode



**Dimensions**

<b>L</b>	3.3mm +/-0.4mm
<b>W</b>	2.6mm +/-0.3mm
<b>T</b>	0.78mm +/-0.20mm
<b>B</b>	0.6mm +/-0.25mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	4000

**General Information**

<b>Style:</b>	SMD Chip
<b>Series:</b>	FloatingFlexTerm-(CxxxxY)
<b>Chip Size:</b>	1210
<b>Description:</b>	SMD, MLCC, FF-CAP, Floating Electrode
<b>Features:</b>	FF-CAP, Floating Electrode
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>Marking:</b>	No
<b>Failure Rate:</b>	N/A
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours

**Specifications**

<b>Capacitance:</b>	0.01 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	200 VDC
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	X7R
<b>Dissipation Factor:</b>	2.5%
<b>Aging Rate:</b>	3% Loss/Decade Hour
<b>Insulation Resistance:</b>	100 GOhms
<b>Dielectric Strength:</b>	500 V