


Polymer Aluminum, 125C LowZ, A759, 330 uF, 20%, 63 V, -55/+125C, 20mm, Lead Spacing = 5mm



Dimensions	
D	13mm +/-0.5mm
L	20mm +/-1mm
S	5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.6mm +/-0.5mm

Packaging Specifications	
Packaging:	Bulk, Bag

General Information	
Dielectric:	Polymer Aluminum
Series:	A759
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads

Specifications	
Capacitance:	330 uF
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.45 VDC (Surge)
Temperature Range:	-55/+125C
Rated Temperature:	125C
Life:	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	12% 120Hz 20C
Resistance:	42 mOhms (100kHz 20C)
Current:	4030 mAmps (100kHz 105C), 2350 mAmps (100kHz 125C)
Impedance Ratio at -25C:	1.25
Impedance Ratio at -55C:	1.25