



THB AC Filtering Metalized Polypropylene Film Capacitor Radial Type 85 °C / 85 % RH 1000 h at U_{NAC}



FEATURES

- High robustness under high humidity
- THB 85 °C, 85 % RH, 1000 h at rated U_{NAC}
- UL 810 (electrical pending)
- Segmented film
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- Outdoor applications
- UPS systems
- Renewable energy
- AC harmonic filter
- Welding equipment

QUICK REFERENCE DATA

Rated capacitance range	1 µF to 35 µF
Capacitance tolerance	± 10 %, ± 5 %
Maximum continuous AC voltage (50 Hz / 60 Hz) range, U _{NAC}	250 V _{AC} , 310 V _{AC} , 350 V _{AC} , 480 V _{AC}
Climatic testing class	40 / 105 / 56 B
Rated temperature	85 °C
Maximum permissible case temperature	105 °C
Reference standards	IEC 61071, IEC 60068, UL 810
Dielectric	Polypropylene film
Electrodes	Metallized dielectric film
Construction	<div style="display: flex; justify-content: space-around;"> <div> <p>Mono construction</p> </div> <div> <p>Series construction</p> </div> </div> <p style="text-align: center;">≤ 310 V_{AC} <</p>
Encapsulation	Plastic case sealed with resin; flame retardant
Terminals	Tinned wire
Self inductance (L _S)	< 1 nH per mm of lead spacing
Withstanding DC voltage between terminals ⁽¹⁾	1.5 U _{NDC} for 10 s, cut off current 10 mA, rise time ≤ 1000 V/s
Insulation resistance	RC between leads, after 1 min > 10 000 s, measuring voltage: 500 V
Life time expectancy ⁽²⁾	FIT: < 10 x 10 ⁻⁹ /h (10 per 10 ⁹ component hours) at 0.5 x U _N , 40 °C
Marking	C-value, tolerance, rated voltage, code for dielectric material, code for manufacturing origin, manufacturer's type designation, manufacturer location, year and week, manufacturer's logo or name


Notes

- For more detailed data and test requirements, contact dc-film@vishay.com
- For general information like characteristics and definitions used for film capacitors follow the link: www.vishay.com/doc?28147
- ⁽¹⁾ See document "Voltage Proof Test for Metalized Capacitors" (www.vishay.com/doc?28169)
- ⁽²⁾ Statements about life time are based on calculations which are based on internal tests. They have to be understood exclusively as estimations. Also due to external factors, the life time in the field application may deviate from the calculated life time.

AC VOLTAGE RATINGS (V_{RMS})

U _{NAC}	250 V	310 V	350 V	480 V
U _{OPAC} at 85 °C	250 V	310 V	350 V	480 V
U _{OPAC} at 105 °C	175 V	210 V	240 V	330 V

COMPOSITION OF CATALOG NUMBER




Note


(1) Tabs terminals or customized terminals are available on request

DIMENSIONS in millimeters

2 PINS



4 PINS



Note

- $\varnothing dt \pm 10 \%$ of standard diameter specified



ELECTRICAL DATA AND ORDERING CODE

U _{RAC} (V)	CAP. (μF)	DIMENSION (mm)			P1 (mm)	P2 (mm)	(dU/dt) _R ⁽¹⁾ (V/μs)	I _{PEAK} (A)	I _{RMS} ⁽²⁾ (A)		ESR ⁽³⁾ 10 kHz (mΩ)		tan δ ⁽⁴⁾ 10 kHz < (x 10 ⁻⁴)		ORDERING CODE ⁽⁵⁾
		w	h	l					2 PINS	4 PINS	2 PINS	4 PINS	2 PINS	4 PINS	
250	U _{OPAC} AT 85 °C = 250 V _{AC} ; U _{OPAC} AT 105 °C = 175 V _{AC} ; C-TOL. = ± 10 % (U _{NDC} = 500 V)														
	1	13.0	23.0	32.0	27.5	-	50	50	3	-	29.5	-	30	-	MKP1847H51025+K2
	2	15.0	25.0	32.0	27.5	-	50	100	4.5	-	15	-	30	-	MKP1847H52025+K2
	3	18.0	28.0	32.0	27.5	-	50	150	6.5	-	10	-	30	-	MKP1847H53025+K2
	4	21.0	31.0	32.0	27.5	-	50	200	8	-	7.5	-	30	-	MKP1847H54025+K2
	5	21.0	31.0	32.0	27.5	-	50	250	9	-	6	-	30	-	MKP1847H55025+K2
	6	22.0	38.0	32.0	27.5	-	50	300	10.5	-	5	-	30	-	MKP1847H56025+K2
	7	22.0	38.0	32.0	27.5	-	50	350	11.5	-	4.5	-	30	-	MKP1847H57025+K2
	8	22.0	38.0	32.0	27.5	-	50	400	12	-	4	-	30	-	MKP1847H58025+K2
	10	21.5	38.5	42.0	37.5	10.2	25	250	9.5	11	7.5	6.5	70	65	MKP1847H61025+P*
	12	30.0	45.0	42.0	37.5	10.2 / 20.3	25	300	12.5	13.5	6	5.5	70	65	MKP1847H61225+P*
	15	30.0	45.0	42.0	37.5	10.2 / 20.3	25	375	14	15	5	4.5	70	65	MKP1847H61525+P*
	20	30.0	45.0	42.0	37.5	10.2 / 20.3	25	500	16	17.5	3.5	3	70	65	MKP1847H62025+P*
	22	30.0	45.0	57.5	52.5	20.3	12	264	13	14.5	7	6	135	120	MKP1847H62225+Y*
	25	30.0	45.0	57.5	52.5	20.3	12	300	14	15.5	6	5.5	135	120	MKP1847H62525+Y*
	30	35.0	50.0	57.5	52.5	20.3	12	360	16.5	18	5	4.5	135	120	MKP1847H63025+Y*
	35	35.0	50.0	57.5	52.5	20.3	12	420	18	19.5	4.5	3.5	135	120	MKP1847H63525+Y*
310	U _{OPAC} AT 85 °C = 310 V _{AC} ; U _{OPAC} AT 105 °C = 210 V _{AC} ; C-TOL. = ± 10 % (U _{NDC} = 630 V)														
	1	13.0	23.0	32.0	27.5	-	65	65	4	-	19	-	25	-	MKP1847H51031+K2
	2	18.0	28.0	32.0	27.5	-	65	130	6.5	-	9.5	-	25	-	MKP1847H52031+K2
	3	21.0	31.0	32.0	27.5	-	65	195	8.5	-	6.5	-	25	-	MKP1847H53031+K2
	4	22.0	38.0	32.0	27.5	-	65	260	11	-	5	-	25	-	MKP1847H54031+K2
	5	21.5	38.5	42.0	37.5	10.2	35	175	9	10	8.5	7.5	50	45	MKP1847H55031+P*
	6	21.5	38.5	42.0	37.5	10.2	35	210	10	11	7	6	50	45	MKP1847H56031+P*
	7	30.0	45.0	42.0	37.5	10.2 / 20.3	35	245	12.5	14	6	5.5	50	45	MKP1847H57031+P*
	8	30.0	45.0	42.0	37.5	10.2 / 20.3	35	280	13.5	14.5	5	4.5	50	45	MKP1847H58031+P*
	10	30.0	45.0	42.0	37.5	10.2 / 20.3	35	350	15	16.5	4	3.5	50	45	MKP1847H61031+P*
	12	30.0	45.0	57.5	52.5	20.3	15	180	13	14.5	7	6	100	85	MKP1847H61231+P*
	15	30.0	45.0	57.5	52.5	20.3	15	225	14.5	16	5.5	5	100	85	MKP1847H61531+Y*
	20	35.0	50.0	57.5	52.5	20.3	15	300	18	19.5	4	3.5	100	85	MKP1847H62031+Y*
22	35.0	50.0	57.5	52.5	20.3	15	330	19	20.5	4	3.5	100	85	MKP1847H62231+Y*	
350	U _{OPAC} AT 85 °C = 350 V _{AC} ; U _{OPAC} AT 105 °C = 240 V _{AC} ; C-TOL. = ± 10 % (U _{NDC} = 700 V)														
	1	15.0	25.0	32.0	27.5	-	80	80	4.5	-	20.5	-	20	-	MKP1847H51035+K2
	2	18.0	28.0	32.0	27.5	-	80	160	7	-	10.5	-	20	-	MKP1847H52035+K2
	3	21.0	31.0	32.0	27.5	-	80	240	9	-	7	-	20	-	MKP1847H53035+K2
	4	22.0	38.0	32.0	27.5	-	80	320	11.5	-	5.5	-	20	-	MKP1847H54035+K2
	5	21.5	38.5	42.0	37.5	10.2	50	250	10.5	11	7.5	7.5	40	35	MKP1847H55035+P*
	6	21.5	38.5	42.0	37.5	10.2	50	300	11.5	12.5	6.5	6	40	35	MKP1847H56035+P*
	7	30.0	45.0	42.0	37.5	10.2 / 20.3	50	350	14	15	6	5.5	40	35	MKP1847H57035+P*
	8	30.0	45.0	42.0	37.5	10.2 / 20.3	50	400	15.5	16.5	5	4.5	40	35	MKP1847H58035+P*
	10	30.0	45.0	42.0	37.5	10.2 / 20.3	50	500	17	19	4	3.5	40	35	MKP1847H61035+P*
	12	30.0	45.0	57.5	52.5	20.3	25	300	15.5	16	6	6	80	70	MKP1847H61235+Y*
	15	30.0	45.0	57.5	52.5	20.3	25	375	17	18.5	5	4.5	80	70	MKP1847H61535+Y*
	20	35.0	50.0	57.5	52.5	20.3	25	500	21	23	4	3.5	80	70	MKP1847H62035+Y*
22	35.0	50.0	57.5	52.5	20.3	25	550	22.5	24.5	3.5	3	80	70	MKP1847H62235+Y*	
480	U _{OPAC} AT 85 °C = 480 V _{AC} ; U _{OPAC} AT 105 °C = 330 V _{AC} ; C-TOL. = ± 10 % (U _{NDC} = 1000 V)														
	2	21.5	38.5	42.0	37.5	10.2	80	160	9	10	9.5	9	20	15	MKP1847H52048+P*
	3	30.0	45.0	42.0	37.5	10.2 / 20.3	80	240	13.5	14	6.5	6	20	15	MKP1847H53048+P*
	4	30.0	45.0	57.5	52.5	20.3	80	320	12.5	13	9	8	40	35	MKP1847H54048+Y*
	5	30.0	45.0	57.5	52.5	20.3	35	175	14.0	14.5	7.5	6.5	40	35	MKP1847H55048+Y*
	6	35.0	50.0	57.5	52.5	20.3	35	210	16.5	17.5	6.5	6	40	35	MKP1847H56048+Y*
	7	35.0	50.0	57.5	52.5	20.3	35	245	18.0	18.5	5.5	5	40	35	MKP1847H57048+Y*

Notes

- (1) Rated voltage pulse slope (dU/dt)_R at voltage U_{NDC}
(2) Maximum RMS current at 10 kHz, +85 °C, capacitance tolerance specified
(3) Equivalent series resistance typical values at f = 10 kHz
(4) Maximum tan δ values
(5) Change the "*" symbol with special code for the terminals and "+" for tolerance




PACKAGING INFORMATION

U _{RAC} (V)	U _{NDC} (V)	CAP. ⁽¹⁾ (μF)	DIMENSION (mm)			Ø dt (mm)	ORDERING CODE ⁽²⁾	MASS (g)	SPQ ⁽³⁾ (pcs)
			w	h	l				
250	500	1	13.0	23.0	32.0	0.8	MKP1847H51025+K2	11	115
		2	15.0	25.0	32.0	0.8	MKP1847H52025+K2	14	100
		3	18.0	28.0	32.0	0.8	MKP1847H53025+K2	18	80
		4	21.0	31.0	32.0	0.8	MKP1847H54025+K2	23	65
		5	21.0	31.0	32.0	0.8	MKP1847H55025+K2	21	65
		6	22.0	38.0	32.0	0.8	MKP1847H56025+K2	24	60
		7	22.0	38.0	32.0	0.8	MKP1847H57025+K2	23	60
		8	22.0	38.0	32.0	0.8	MKP1847H58025+K2	22	60
		10	21.5	38.5	42.0	1.0	MKP1847H61025+P*	35	91
		12	30.0	45.0	42.0	1.0	MKP1847H61225+P*	68	63
		15	30.0	45.0	42.0	1.0	MKP1847H61525+P*	64	63
		20	30.0	45.0	42.0	1.0	MKP1847H62025+P*	56	63
		22	30.0	45.0	57.5	1.2	MKP1847H62225+Y*	73	45
		25	30.0	45.0	57.5	1.2	MKP1847H62525+Y*	69	45
		30	35.0	50.0	57.5	1.2	MKP1847H63025+Y*	95	40
		35	35.0	50.0	57.5	1.2	MKP1847H63525+Y*	86	40
310	630	1	13.0	23.0	32.0	0.8	MKP1847H51031+K2	10	115
		2	18.0	28.0	32.0	0.8	MKP1847H52031+K2	17	80
		3	21.0	31.0	32.0	0.8	MKP1847H53031+K2	21	65
		4	22.0	38.0	32.0	0.8	MKP1847H54031+K2	24	60
		5	21.5	38.5	42.0	1.0	MKP1847H55031+P*	38	91
		6	21.5	38.5	42.0	1.0	MKP1847H56031+P*	36	91
		7	30.0	45.0	42.0	1.0	MKP1847H57031+P*	70	63
		8	30.0	45.0	42.0	1.0	MKP1847H58031+P*	67	63
		10	30.0	45.0	42.0	1.0	MKP1847H61031+P*	62	63
		12	30.0	45.0	57.5	1.2	MKP1847H61231+Y*	77	45
		15	30.0	45.0	57.5	1.2	MKP1847H61531+Y*	70	45
		20	35.0	50.0	57.5	1.2	MKP1847H62031+Y*	90	40
		22	35.0	50.0	57.5	1.2	MKP1847H62231+Y*	86	40
350	700	1	15.0	25.0	32.0	0.8	MKP1847H51035+K2	16	100
		2	18.0	28.0	32.0	0.8	MKP1847H52035+K2	22	80
		3	21.0	31.0	32.0	0.8	MKP1847H53035+K2	28	65
		4	22.0	38.0	32.0	0.8	MKP1847H54035+K2	34	60
		5	21.5	38.5	42.0	1.0	MKP1847H55035+P*	51	91
		6	21.5	38.5	42.0	1.0	MKP1847H56035+P*	49	91
		7	30.0	45.0	42.0	1.0	MKP1847H57035+P*	83	63
		8	30.0	45.0	42.0	1.0	MKP1847H58035+P*	81	63
		10	30.0	45.0	42.0	1.0	MKP1847H61035+P*	77	63
		12	30.0	45.0	57.5	1.2	MKP1847H61235+Y*	121	45
		15	30.0	45.0	57.5	1.2	MKP1847H61535+Y*	119	45
		20	35.0	50.0	57.5	1.2	MKP1847H62035+Y*	150	40
480	1000	22	35.0	50.0	57.5	1.2	MKP1847H62235+Y*	146	40
		2	21.5	38.5	42.0	1.0	MKP1847H52048+P*	49	91
		3	30.0	45.0	42.0	1.0	MKP1847H53048+P*	77	63
		4	30.0	45.0	57.5	1.2	MKP1847H54048+Y*	121	45
		5	30.0	45.0	57.5	1.2	MKP1847H55048+Y*	119	45
		6	35.0	50.0	57.5	1.2	MKP1847H56048+Y*	152	40
		7	35.0	50.0	57.5	1.2	MKP1847H57048+Y*	147	40

Notes

- (1) Intermediate capacitance values available on request
 (2) Change the "*" symbol with special code for the terminals and "+" for tolerance
 (3) SPQ = Standard Packing Quantity

APPROVALS				
SAFETY APPROVALS	VOLTAGE	VALUE	FILE NUMBERS	LINKS
UL 810 construction	Up to 480 V _{AC}	1 µF to 35 µF	Pending	www.vishay.com/doc?
				

CONSTRUCTION DESCRIPTION

Low inductive wound cell elements of metallized polypropylene film, potted with resin in a flame retardant case.

SPECIFIC METHOD OF MOUNTING TO WITHSTAND VIBRATION AND SHOCK

The capacitor unit is designed for mounting on a printed circuit board.

In order to withstand vibration and shock tests, it must be insured that the stand-off pips are in good contact with the printed circuit board.

The capacitors shall be mechanically fixed by the leads and the body clamped.

DIMENSIONS TOLERANCES

For the maximum product dimensions for length ($l_{max.}$), width ($w_{max.}$) and height ($h_{max.}$) use the following tolerances:

$$l_{max.} = l + \Delta l, w_{max.} = w + \Delta w, \text{ and } h_{max.} = h + \Delta h$$

$$\text{Pitch} = 27.5 \text{ mm}, \Delta w = \Delta l = 0.5 \text{ mm}, \text{ and } \Delta h = 0.1 \text{ mm}$$

$$\text{Pitch} = 37.5 \text{ mm}, \Delta w = \Delta l = 0.7 \text{ mm}, \text{ and } \Delta h = 0.5 \text{ mm}$$

$$\text{Pitch} = 52.5 \text{ mm}, \Delta w = \Delta l = 1.0 \text{ mm}, \text{ and } \Delta h = 0.5 \text{ mm}$$

$$l_{min.} = l - \Delta l, w_{min.} = w - \Delta w \text{ and } h_{min.} = h - \Delta h$$

$$\text{Pitch} = 27.5 \text{ mm}, \Delta l = 1.0 \text{ mm}, \text{ and } \Delta w = \Delta h = 0.5 \text{ mm}$$

$$\text{Pitch} = 37.5 \text{ mm}, \Delta l = 1.0 \text{ mm}, \text{ and } \Delta w = \Delta h = 1.0 \text{ mm}$$

$$\text{Pitch} = 52.5 \text{ mm}, \Delta l = 1.5 \text{ mm}, \text{ and } \Delta w = \Delta h = 1.0 \text{ mm}$$

SPACE REQUIREMENTS ON PRINTED-CIRCUIT BOARD

For product height with seating plane as given by "IEC 60717" as reference.


For 2 pins:

The maximum space for length ($l_{max.}$), width ($w_{max.}$), and height ($h_{max.}$) of film capacitors to take in account on the printed circuit board is shown in the drawings.


- For products with pitch ≤ 27.5 mm, $\Delta w = \Delta l = 0.5$ mm, and $\Delta h = 0.1$ mm
- For products with pitch = 37.5 mm, $\Delta w = \Delta l = 0.7$ mm, and $\Delta h = 0.5$ mm
- For products with pitch = 52.5 mm, $\Delta w = \Delta l = 1.0$ mm, and $\Delta h = 0.5$ mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.

The maximum length and width of film capacitors is shown in the figure:



For 4 pins:

DIMENSIONS in millimeters				
				
P1	L _{max.}	W _{max.}	Ø D	H
37.5	l + 1.5	w + 1.8	1.5	h + 0.5
52.5	l + 1.8	w + 2.0	1.7	h + 0.5

SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile we refer to the document “Characteristics and Definitions Used for Film Capacitors”: www.vishay.com/doc?26033.

STORAGE TEMPERATURE

T_{stg} = -25 °C to +35 °C with relative humidity of maximum 75 % without condensation


RATINGS AND CHARACTERISTICS REFERENCE CONDITIONS

Unless otherwise specified, all electrical values apply to an ambient temperature of 23 °C ± 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % ± 2 %.


For reference testing, a conditioning period shall be applied over 96 h ± 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.




CHARACTERISTICS




Capacitance as a function of ambient temperature (typical)




Insulation resistance as a function of ambient temperature (typical)




RMS voltage in function of temperature




Impedance vs. Frequency (typical)




Impedance vs. Frequency (typical)




Impedance vs. Frequency (typical)




Maximum RMS voltage as function of frequency
 $T_{amb} \leq 85^\circ C$; $U_n = 250 V_{AC}$




Maximum RMS voltage as function of frequency
 $T_{amb} \leq 85^\circ C$; $U_n = 310 V_{AC}$




Maximum RMS voltage as function of frequency
 $T_{amb} \leq 85^\circ C$; $U_n = 350 V_{AC}$




Maximum RMS voltage as function of frequency
 $T_{amb} \leq 85^\circ C$; $U_n = 480 V_{AC}$




Maximum RMS current as function of frequency
 $T_{amb} \leq 85^\circ C$; $U_n = 250 V_{AC}$



Maximum RMS current as function of frequency
 $T_{amb} \leq 85^\circ C$; $U_n = 310 V_{AC}$



Maximum RMS current as function of frequency
 $T_{amb} \leq 85^{\circ}\text{C}$; $U_n = 350\text{ V}_{AC}$



Maximum RMS current as function of frequency
 $T_{amb} \leq 85^{\circ}\text{C}$; $U_n = 480\text{ V}_{AC}$

HEAT CONDUCTIVITY			
DIMENSION (mm)			HEAT CONDUCTIVITY (mW/°C)
w	h	l	
13.0	23.0	32.0	22
15.0	25.0	32.0	25
18.0	28.0	32.0	30
21.0	31.0	32.0	35
22.0	38.0	32.0	41
21.5	38.5	42.0	52
30.0	45.0	42.0	70
30.0	45.0	57.5	86
35.0	50.0	57.5	100


POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free air ambient temperature.

The component temperature rise (ΔT) can be measured or calculated by $\Delta T = P/G$:

- ΔT = component temperature rise ($^{\circ}\text{C}$) with a maximum of 15°C
- P = power dissipation of the component (mW)
- G = heat conductivity of the component (mW/ $^{\circ}\text{C}$)

MEASURING THE COMPONENT TEMPERATURE



The case temperature is measured in unloaded condition (T_{amb}) and loaded condition (T_C).

The temperature rise is given by $\Delta T = T_C - T_{amb}$.

To avoid thermal radiation or convection, the capacitor must be tested in a closed area from air circulation.

**APPLICATION NOTES AND LIMITING CONDITIONS**

These capacitors are not suitable for mains applications as across-the-line capacitors without additional protection. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

To select the capacitor for a certain application, the following conditions must be checked:

1. The peak voltage (U_{p+}) shall not be greater than $\sqrt{2} \times U_{RMS}$
2. The peak-to-peak ripple voltage (U_{pp}) shall not be greater than $2 \times \sqrt{2} \times U_{RMS}$ (for U_{RMS} consult graph "Maximum RMS Voltage as Function of Frequency")
3. The voltage pulse slope (dU/dt) shall not exceed the rated pulse slope at the DC voltage rating.
If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by U_{NDC} and divided by the applied voltage.

$$2 \times \int_0^T \left(\frac{dU}{dt} \right)^2 \times dt < U_{NDC} \times \left(\frac{dU}{dt} \right)_{rated}$$

T is the pulse duration

4. The maximum component surface temperature must be lower than 105 °C and maximum temperature rise between case and free air ambient shall be lower than 15 °C.

INSPECTION REQUIREMENTS					
SUB-CLAUSE NUMBER AND TEST		CONDITIONS	PERFORMANCE REQUIREMENTS		
ROUTINE TEST - FINAL INSPECTION					
5.14.2-1 External inspection, visual examination		1 kHz at room temperature	Legible marking as specified		
5.14.2-2 Dimensions			See specification drawing		
5.3-1 Capacitance			See specific reference data		
5.3-2 tan δ			See specific reference data		
5.5.1-2 Voltage test between terminals		1.5 x U _{NDC} at T _{amb} Duration: 2 s	No visible damage or puncture No flashover		
5.7 Insulation resistance		Measuring voltage 500 V at room temperature Duration: 1 min	See specific reference data		
TYPE TESTS					
5.14.2 External inspection		Check for finish, marking, and overall dimensions	Legible marking and finish as specified Dimensions: see specification drawing		
5.14.0 Initial measurements		Capacitance at 1 kHz tan δ at 10 kHz			
5.14.1-1/4 Robustness of terminations IEC 60068-2-21		Tensile U _{a1}			
		Wire diameter		Section	Load
		d ≤ 0.80 mm		S ≤ 0.5 mm ²	10 N (± 10 %)
		d ≤ 1.25 mm		S ≤ 1.2 mm ²	20 N (± 10 %)
		Duration: 10 s ± 1 s			
		Bending, U _b method 1			
		Wire diameter		Section modulus	Load
		d ≤ 0.80 mm		Z _x ≤ 0.05 mm ³	5 N (10 %)
		d ≤ 1.25 mm		Z _x ≤ 0.019 mm ³	10 N (± 10 %)
		4 x 90°, duration: 2 s to 3 s/bend			
5.14.1-6 Resistance to soldering heat IEC 60068-2-20		No pre-drying, method 1A Solder bath: 280 °C ± 5 °C Duration: 10 s ± 1 s			
5.14.4 Final measurements		Capacitance tan δ			
		ΔC/C ≤ 0.5 % Increase of tan δ ≤ 0.0050 compared to the values measured in 5.14.0			

INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
5.14.0 Initial measurements	Capacitance at 1 kHz tan δ at 10 kHz	No visible damage
5.14.3-1 Vibration IEC 60068-2-6	10 Hz to 55 Hz; a = ± 0.35 mm or acceleration 98 m/s ² Test duration: 10 frequency cycles (3 axes offset from each other by 90°) 1 octave/min Visual examination	
5.14.3-2 Shock or impact IEC 60068-2-6	Pulse shape: half sine Acceleration: 490 m/s ² Duration of pulse: 11 ms	
5.14.4 Final measurements	Visual examination Capacitance tan δ	
5.5.3-1 Initial measurements	Capacitance at 1 kHz tan δ at 10 kHz R insulation	ΔC/C ≤ 0.5 % Increase of tan δ ≤ 0.0050 compared to the values measured in 5.14.0
5.5.3-2 DC voltage test between terminals	1.5 x U _{NDC} at T _{amb} Duration: 10 s	
5.5.3-3 Final measurements	Capacitance tan δ R insulation	
5.9-1 Initial measurements	Capacitance at 1 kHz tan δ at 10 kHz	ΔC/C ≤ 0.5 % Increase of tan δ ≤ 0.0050 R insulation ≥ 50 % of specified values
5.9-2 Surge discharge test	1.1 x U _{NDC} Number of discharges: 5 Time lapse: every 2 min (10 min total)	
5.9-2 DC voltage test between terminals	Within 5 min after the surge discharge test Duration: 10 s 1.5 x U _{NDC} at T _{amb}	
5.9-3 Final measurements	Capacitance tan δ	
5.11-1 Initial measurements	Capacitance at 1 kHz tan δ at 10 kHz	Number of clearings ≤ 5 Clearing = voltage drop of 5 %
5.11-2 Self healing test	1.5 x U _{NDC} , duration: 10 s Increase the voltage at 100 V/s till 5 clearings occur or until voltage reach max. of 2.5 x U _{NDC} for a duration of 10 s	
5.11-3 Final measurements	Capacitance tan δ	
		ΔC/C ≤ 0.5 % tan δ ≤ 1.2 x initial tan δ + 0.0001 compared to the values measured in 5.11-1



INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
5.13-0 Initial measurements 5.13-1 Change of temperature according to IEC 60068-2-14 5.13-2 Damp heat steady state according to IEC 60068-2-78 5.5.3-2 DC voltage test between terminals 5.13-3 Final measurements	Capacitance at 1 kHz tan δ at 10 kHz Test Nb $T_{max.} = +105\text{ }^{\circ}\text{C}$ $T_{min.} = -40\text{ }^{\circ}\text{C}$ Transition time: 1 h, equivalent to 1 $^{\circ}\text{C}/\text{min}$. 5 cycles Test Ca $T = 40\text{ }^{\circ}\text{C} \pm 2\text{ }^{\circ}\text{C}$ $RH = 93\text{ \%} \pm 3\text{ \%}$ Duration: 56 days $1.5 \times U_{NDC}$ at ambient temperature Duration: 10 s Visual examination Capacitance tan δ	No puncturing or flashover Self healing punctures are permitted $ \Delta C/C \leq 2.0\text{ \%}$ Increase of tan $\delta \leq 0.0150$ compared to the values measured in 5.13-0
5.13A-0 Initial measurements 5.13A.2 Damp heat steady state with load 5.13.3 Final measurements	Capacitance at 1 kHz tan δ at 1 kHz $T = 85\text{ }^{\circ}\text{C}$ $RH = 85\text{ \%}$ at U_N Duration: 1000 h Capacitance at 1 kHz tan δ R insulation	$ \Delta C/C < 10\text{ \%}$ Increase of tan δ : ≤ 0.008 for: $C \leq 10\text{ }\mu\text{F}$ or ≤ 0.005 for: $C > 10\text{ }\mu\text{F}$ Compared to the values measured in 5.13A-0 R insulation $\geq 50\text{ \%}$ of specified values
5.10-0 Initial measurements 5.10-1 Thermal stability test under overload conditions 5.10-2 Final measurements	Capacitance at 1 kHz tan δ at 10 kHz Natural cooling $T_{amb} \pm 5\text{ }^{\circ}\text{C}$ $1.21 \times P_{max.} = 1.21 \times (I_{RMS}^2/w \times C) \times \tan \delta(f)$ with $w = 2 \times \pi \times f$ For I_{RMS} see specific reference data $f = 10\text{ kHz}$ Duration: 48 h Measure the temperature every 1.5 h during the last 6 h Capacitance tan δ at 10 kHz	Temperature rise $< 1\text{ }^{\circ}\text{C}$ $ \Delta C/C \leq 2.0\text{ \%}$ Increase of tan $\delta \leq 0.0150$



INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
5.12 Resonance frequency measurement	Impedance analyzer at T_{amb}	> 0.9 times the value as specified in typical curve "Resonant frequency" of this specification
5.15-0 Initial measurements	Capacitance at 1 kHz $\tan \delta$ at 10 kHz	
5.15-1 Endurance test between terminals	Sequence: 1.25 x (U_{RMS} at 85 °C) at $T_{max.} = 85$ °C 1.25 x (U_{RMS} at 105 °C) at $T_{max.} = 105$ °C Duration: 500 h 1000 x discharge at $1.4 \times \hat{I}$ (maximum peak current) 1.25 x (U_{RMS} at 85 °C) at $T_{max.} = 85$ °C 1.25 x (U_{RMS} at 105 °C) at $T_{max.} = 105$ °C Duration: 500 h	
5.15-2 Final measurement	Capacitance $\tan \delta$	$ \Delta C/C \leq 3.0$ % Increase of $\tan \delta \leq 0.0150$ compared to the values measured in 5.15-0
5.16.3-0 Initial measurements	Capacitance at 1 kHz	
5.16.3-1 Destruction test sequence for segmented film	The capacitors must be put in an oven at $T_{max.} = 105$ °C/2 h and cooled down Product enveloped with cheese cloth	
High DC voltage test (limited to 200 mA)	3 x U_{NDC} with minimum 2000 V_{DC} , duration = 1 min Discharge the capacitor, duration = 1 min	DC power supply capable of obtaining the desired breakdown voltage
High AC voltage test	AC_{RMS} voltage = 1 x U_N , duration = 15 s The above sequence shall be repeated until the test sample capacitance loss 10 % of its initial measurement in 5.16.3B-0	No burning of the cheese cloth
5.16.3-2 Final measurements	Visual examination Capacitance at 1 kHz	The dielectric must withstand the test sequence conducted

Note

- Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 61071".



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.