


Aluminum Electrolytic, 85C, ALC10, 470 uF, 20%, 450 V, -40/+85C



General Information	
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Series:</b>	ALC10
<b>Description:</b>	Snap-In, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Lead:</b>	2 Pin
<b>Notes:</b>	Dimensions D And L Include Slewing

Dimensions	
<b>D</b>	35mm +1mm
<b>L</b>	50mm +/-2mm
<b>S</b>	10mm +/-0.1mm
<b>LL</b>	6.3mm +/-1mm
<b>F</b>	2mm +/-0.1mm

Packaging Specifications	
<b>Weight:</b>	70 g
<b>Slewing:</b>	Yes
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	100

Specifications	
<b>Capacitance:</b>	470 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	450 VDC, 495 VDC (Surge)
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	85C
<b>Life:</b>	15000 Hrs (Rated Voltage And Ripple Current At 85C), 24000 Hrs (Rated Voltage At 85C)
<b>Resistance:</b>	252 mOhms (100Hz 20C), 155 mOhms (10kHz 20C)
<b>Current:</b>	2.43 Amps (100Hz 85C), 4.03 Amps (10kHz 85C)
<b>Leakage:</b>	1269 uAmps (5min 20C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.