



## RG59 Style Coaxial Cable

**Product Type:**  
Coaxial Cable

**Application:**

Used to carry baseband video in CCTV applications, previously used for cable television. In general, it has poor shielding but will carry an HQ HD signal or video over short distances. Conductor size is approx 20AWG, so smaller than RG6 or RG11

**Standards:**

REACH and RoHS compliant

**Construction:**

Conductor	Solid copper clad steel conductor
Insulation	Solid polyethylene.
Screen	Copper clad aluminium braid.
Sheath	PVC, Black. Other colours available

**Technical Information:**

Cable diameter	6.1mm nominal
Rated temperature	70°C
Conductor resistance	≤ 235 Ω/km
Insulation resistance	>1000M Ω.km
Nominal velocity ratio	66.7%
Capacitance	<70pF/m
Impedance	75 ± 3 Ω

Attenuation / dB/100m @ 20° C ± 5%

10 MHz	< 3.5
50 MHz	< 8.5
100 MHz	< 11.5
200 MHz	< 16.8
450 MHz	< 26.0
600 MHz	< 30.5
860 MHz	< 37.5
1000 MHz	< 39.5