


KEMET Part Number: C1206V683KCRACTU
(C1206V683KCRAC7800)

Ceramic, Anti-Arcing, ArcShield-(CxxxxV), 0.068 uF, 10%, 500 V, 1206, X7R, SMD, MLCC, ArcShield, High Voltage, Temperature Stable



Dimensions

L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
T	1.7mm +/-0.20mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2000

General Information

Style:	SMD Chip
Series:	ArcShield-(CxxxxV)
Chip Size:	1206
Description:	SMD, MLCC, ArcShield, High Voltage, Temperature Stable
Features:	High Voltage, Temperature Stable
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours. X7R dielectric is not recommended for AC line filtering or pulse applications

Specifications

Capacitance:	0.068 uF
Capacitance Tolerance:	10%
Voltage DC:	500 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	1.47 GOhms
Dielectric Strength:	750 V