


KEMET Part Number: C1210V473KDRACTU
(C1210V473KDRAC7800)



Ceramic, Anti-Arcing, ArcShield-(CxxxxV), 0.047 uF, 10%, 1,000 V, 1210, X7R, SMD, MLCC, ArcShield, High Voltage, Temperature Stable



CeramicChipSolutions
© 2014 KEMET, Inc.
All rights reserved

Dimensions	
L	3.2mm +/-0.2mm
W	2.5mm +/-0.2mm
T	2.1mm +/-0.20mm
B	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2000

General Information	
Style:	SMD Chip
Series:	ArcShield-(CxxxxV)
Chip Size:	1210
Description:	SMD, MLCC, ArcShield, High Voltage, Temperature Stable
Features:	High Voltage, Temperature Stable
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours. X7R dielectric is not recommended for AC line filtering or pulse applications

Specifications	
Capacitance:	0.047 uF
Capacitance Tolerance:	10%
Voltage DC:	1000 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	2.13 GOhms
Dielectric Strength:	1,200 V

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2017 IntelliData.net