

**KEMET Part Number: C0603C105M3RACTU**  
(C0603C105M3RAC7867)

Ceramic, Commercial-(CxxxxC), 1 uF, 20%, 25 V, 0603, X7R, SMD, MLCC, Temperature Stable, Class II



**Dimensions**

|          |                  |
|----------|------------------|
| <b>L</b> | 1.6mm +/-0.15mm  |
| <b>W</b> | 0.8mm +/-0.15mm  |
| <b>T</b> | 0.8mm +/-0.15mm  |
| <b>S</b> | 0.7mm MIN        |
| <b>B</b> | 0.35mm +/-0.15mm |

**Packaging Specifications**

|                            |                        |
|----------------------------|------------------------|
| <b>Packaging:</b>          | T&R, 180mm, Paper Tape |
| <b>Packaging Quantity:</b> | 4000                   |

**General Information**

|                       |  |
|-----------------------|--|
| <b>Style:</b>         | SMD Chip   |
| <b>Series:</b>        | Commercial-(CxxxxC)  |
| <b>Chip Size:</b>     | 0603   |
| <b>Description:</b>   | SMD, MLCC, Temperature Stable, Class II                                |
| <b>Features:</b>      | Temperature Stable, Class II   |
| <b>RoHS:</b>          | Yes  |
| <b>Termination:</b>   | Tin  |
| <b>Marking:</b>       | No   |
| <b>Failure Rate:</b>  | N/A  |
| <b>Miscellaneous:</b> | Note: Referee time for X7R dielectric for this part number is 48 hours |

**Specifications**

|                                 |                     |
|---------------------------------|---------------------|
| <b>Capacitance:</b>             | 1 uF                |
| <b>Capacitance Tolerance:</b>   | 20%                 |
| <b>Voltage DC:</b>              | 25 VDC              |
| <b>Temperature Range:</b>       | -55/+125C           |
| <b>Temperature Coefficient:</b> | X7R                 |
| <b>Dissipation Factor:</b>      | 10%                 |
| <b>Aging Rate:</b>              | 3% Loss/Decade Hour |
| <b>Insulation Resistance:</b>   | 500 MOhms           |
| <b>Dielectric Strength:</b>     | 62.5 V              |