



Is Now Part of



**ON Semiconductor®**

To learn more about ON Semiconductor, please visit our website at  
[www.onsemi.com](http://www.onsemi.com)

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

# FDB86102LZ

## N-Channel PowerTrench® MOSFET 100 V, 30 A, 24 mΩ

### Features

- Max  $r_{DS(on)}$  = 24 mΩ at  $V_{GS} = 10$  V,  $I_D = 8.3$  A
- Max  $r_{DS(on)}$  = 35 mΩ at  $V_{GS} = 4.5$  V,  $I_D = 6.8$  A
- HBM ESD protection level > 6 kV typical (Note 4)
- Very low  $Q_g$  and  $Q_{gd}$  compared to competing trench technologies
- Fast switching speed
- 100% UIL Tested
- RoHS Compliant





### General Description

This N-Channel MOSFET is produced using Fairchild Semiconductor's advanced PowerTrench® process that has been especially tailored to minimize the on-state resistance and switching loss. G-S zener has been added to enhance ESD voltage level.

### Applications

- DC-DC conversion
- Inverter
- Synchronous Rectifier



### MOSFET Maximum Ratings $T_A = 25$ °C unless otherwise noted

| Symbol         | Parameter                                                | Ratings     | Units |
|----------------|----------------------------------------------------------|-------------|-------|
| $V_{DS}$       | Drain to Source Voltage                                  | 100         | V     |
| $V_{GS}$       | Gate to Source Voltage                                   | ±20         | V     |
| $I_D$          | Drain Current -Continuous(Package limited) $T_C = 25$ °C | 30          | A     |
|                | -Continuous (Silicon limited) $T_C = 25$ °C              | 40          |       |
|                | -Continuous $T_A = 25$ °C (Note 1a)                      | 8.3         |       |
|                | -Pulsed                                                  | 50          |       |
| $E_{AS}$       | Single Pulse Avalanche Energy (Note 3)                   | 121         | mJ    |
| $P_D$          | Power Dissipation $T_A = 25$ °C (Note 1a)                | 3.1         | W     |
|                | Power Dissipation $T_A = 25$ °C (Note 1b)                | 2           |       |
| $T_J, T_{STG}$ | Operating and Storage Junction Temperature Range         | -55 to +150 | °C    |

### Thermal Characteristics

|                 |                                                   |     |      |
|-----------------|---------------------------------------------------|-----|------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case (Note 1)     | 1.9 | °C/W |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient (Note 1a) | 40  |      |

### Package Marking and Ordering Information

| Device Marking | Device     | Package  | Reel Size | Tape Width | Quantity  |
|----------------|------------|----------|-----------|------------|-----------|
| FDB86102LZ     | FDB86102LZ | TO-263AB | 330mm     | 24 mm      | 800 units |

**Electrical Characteristics**  $T_J = 25\text{ }^\circ\text{C}$  unless otherwise noted

| Symbol | Parameter | Test Conditions | Min | Typ | Max | Units |
|--------|-----------|-----------------|-----|-----|-----|-------|
|--------|-----------|-----------------|-----|-----|-----|-------|

**Off Characteristics**

|                                      |                                           |                                                                           |     |    |          |                      |
|--------------------------------------|-------------------------------------------|---------------------------------------------------------------------------|-----|----|----------|----------------------|
| $BV_{DSS}$                           | Drain to Source Breakdown Voltage         | $I_D = 250\text{ }\mu\text{A}$ , $V_{GS} = 0\text{ V}$                    | 100 |    |          | V                    |
| $\frac{\Delta BV_{DSS}}{\Delta T_J}$ | Breakdown Voltage Temperature Coefficient | $I_D = 250\text{ }\mu\text{A}$ , referenced to $25\text{ }^\circ\text{C}$ |     | 69 |          | mV/ $^\circ\text{C}$ |
| $I_{DSS}$                            | Zero Gate Voltage Drain Current           | $V_{DS} = 80\text{ V}$ , $V_{GS} = 0\text{ V}$                            |     |    | 1        | $\mu\text{A}$        |
| $I_{GSS}$                            | Gate to Source Leakage Current            | $V_{GS} = \pm 20\text{ V}$ , $V_{DS} = 0\text{ V}$                        |     |    | $\pm 10$ | $\mu\text{A}$        |

**On Characteristics**

|                                        |                                                          |                                                                                   |     |     |     |                      |
|----------------------------------------|----------------------------------------------------------|-----------------------------------------------------------------------------------|-----|-----|-----|----------------------|
| $V_{GS(th)}$                           | Gate to Source Threshold Voltage                         | $V_{GS} = V_{DS}$ , $I_D = 250\text{ }\mu\text{A}$                                | 1.0 | 1.5 | 3.0 | V                    |
| $\frac{\Delta V_{GS(th)}}{\Delta T_J}$ | Gate to Source Threshold Voltage Temperature Coefficient | $I_D = 250\text{ }\mu\text{A}$ , referenced to $25\text{ }^\circ\text{C}$         |     | -6  |     | mV/ $^\circ\text{C}$ |
| $r_{DS(on)}$                           | Static Drain to Source On Resistance                     | $V_{GS} = 10\text{ V}$ , $I_D = 8.3\text{ A}$                                     |     | 18  | 24  | m $\Omega$           |
|                                        |                                                          | $V_{GS} = 4.5\text{ V}$ , $I_D = 6.8\text{ A}$                                    |     | 23  | 35  |                      |
|                                        |                                                          | $V_{GS} = 10\text{ V}$ , $I_D = 8.3\text{ A}$ , $T_J = 125\text{ }^\circ\text{C}$ |     | 31  | 42  |                      |
| $g_{FS}$                               | Forward Transconductance                                 | $V_{DS} = 5\text{ V}$ , $I_D = 8.3\text{ A}$                                      |     | 29  |     | S                    |

**Dynamic Characteristics**

|           |                              |                                                                        |  |     |      |          |
|-----------|------------------------------|------------------------------------------------------------------------|--|-----|------|----------|
| $C_{iss}$ | Input Capacitance            | $V_{DS} = 50\text{ V}$ , $V_{GS} = 0\text{ V}$ ,<br>$f = 1\text{ MHz}$ |  | 959 | 1275 | pF       |
| $C_{oss}$ | Output Capacitance           |                                                                        |  | 181 | 240  | pF       |
| $C_{rss}$ | Reverse Transfer Capacitance |                                                                        |  | 9   | 13   | pF       |
| $R_g$     | Gate Resistance              |                                                                        |  | 0.4 |      | $\Omega$ |

**Switching Characteristics**


|              |                               |                                                                                                         |                                                  |      |    |    |
|--------------|-------------------------------|---------------------------------------------------------------------------------------------------------|--------------------------------------------------|------|----|----|
| $t_{d(on)}$  | Turn-On Delay Time            | $V_{DD} = 50\text{ V}$ , $I_D = 8.3\text{ A}$ ,<br>$V_{GS} = 10\text{ V}$ , $R_{GEN} = 6\text{ }\Omega$ |                                                  | 6.6  | 13 | ns |
| $t_r$        | Rise Time                     |                                                                                                         |                                                  | 2.1  | 10 | ns |
| $t_{d(off)}$ | Turn-Off Delay Time           |                                                                                                         |                                                  | 18.2 | 33 | ns |
| $t_f$        | Fall Time                     |                                                                                                         |                                                  | 2.3  | 10 | ns |
| $Q_{g(TOT)}$ | Total Gate Charge             | $V_{GS} = 0\text{ V}$ to $10\text{ V}$                                                                  | $V_{DD} = 50\text{ V}$ ,<br>$I_D = 8.3\text{ A}$ | 15.2 | 21 | nC |
| $Q_{g(TOT)}$ | Total Gate Charge             | $V_{GS} = 0\text{ V}$ to $4.5\text{ V}$                                                                 |                                                  | 7.6  | 11 | nC |
| $Q_{gs}$     | Gate to Source Charge         |                                                                                                         |                                                  | 2.4  |    | nC |
| $Q_{gd}$     | Gate to Drain "Miller" Charge |                                                                                                         |                                                  | 2.5  |    | nC |

**Drain-Source Diode Characteristics**

|          |                                       |                                                           |  |     |     |    |
|----------|---------------------------------------|-----------------------------------------------------------|--|-----|-----|----|
| $V_{SD}$ | Source to Drain Diode Forward Voltage | $V_{GS} = 0\text{ V}$ , $I_S = 8.3\text{ A}$ (Note 2)     |  | 0.8 | 1.3 | V  |
|          |                                       | $V_{GS} = 0\text{ V}$ , $I_S = 2.4\text{ A}$ (Note 2)     |  | 0.7 | 1.2 |    |
| $t_{rr}$ | Reverse Recovery Time                 | $I_F = 8.3\text{ A}$ , $di/dt = 100\text{ A}/\mu\text{s}$ |  | 42  | 67  | ns |
| $Q_{rr}$ | Reverse Recovery Charge               |                                                           |  | 40  | 64  | nC |

## NOTES:

1.  $R_{\theta JA}$  is determined with the device mounted on a 1 in<sup>2</sup> pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a) 40  $^\circ\text{C}/\text{W}$  when mounted on a 1 in<sup>2</sup> pad of 2 oz copper



b) 62.5  $^\circ\text{C}/\text{W}$  when mounted on a minimum pad of 2 oz copper

2. Pulse Test: Pulse Width < 300  $\mu\text{s}$ , Duty cycle < 2.0 %.

3. Starting  $T_J = 25\text{ }^\circ\text{C}$ ,  $L = 3\text{ mH}$ ,  $I_{AS} = 9\text{ A}$ ,  $V_{DD} = 100\text{ V}$ ,  $V_{GS} = 10\text{ V}$ .

4. The diode connected between gate and source serves only as protection against ESD. No gate overvoltage rating is implied.

## Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 1. On Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

## Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Gate Leakage Current vs Gate to Source Voltage




Figure 11. Maximum Continuous Drain Current vs Case Temperature




Figure 12. Forward Bias Safe Operating Area

# Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 13. Single Pulse Maximum Power Dissipation





Figure 14. Junction-to-Case Transient Thermal Response Curve



## TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

|                                                                                     |                                                                                     |                                                                                            |                                                                                             |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|
| AccuPower™                                                                          | FPS™                                                                                | Power-SPM™                                                                                 | The Power Franchise®                                                                        |
| Auto-SPM™                                                                           | F-PFS™                                                                              | PowerTrench®                                                                               | The Right Technology for Your Success™                                                      |
| AX-CAP™*                                                                            | FRFET®                                                                              | PowerXS™                                                                                   | the power franchise                                                                         |
| BitSiC®                                                                             | Global Power ResourceSM                                                             | Programmable Active Droop™                                                                 | TinyBoost™                                                                                  |
| Build it Now™                                                                       | Green FPS™                                                                          | QFET®                                                                                      | TinyBuck™                                                                                   |
| CorePLUS™                                                                           | Green FPS™ e-Series™                                                                | QS™                                                                                        | TinyCalc™                                                                                   |
| CorePOWER™                                                                          | Gmax™                                                                               | Quiet Series™                                                                              | TinyLogic™                                                                                  |
| CROSSVOLT™                                                                          | GTO™                                                                                | RapidConfigure™                                                                            | TINYOPTO™                                                                                   |
| CTL™                                                                                | IntelliMAX™                                                                         |  ™        | TinyPower™                                                                                  |
| Current Transfer Logic™                                                             | ISOPANAR™                                                                           |  ™        | TinyPWM™                                                                                    |
| DEUXPEED®                                                                           | MegaBuck™                                                                           | Saving our world, 1mW/W/kW at a time™                                                      | TinyWire™                                                                                   |
| Dual Cool™                                                                          | MICROCOUPLER™                                                                       | SignalWise™                                                                                | TranSiC™                                                                                    |
| EcoSPARK®                                                                           | MicroFET™                                                                           | SmartMax™                                                                                  | TriFault Detect™                                                                            |
| EfficientMax™                                                                       | MicroPak™                                                                           | SMART START™                                                                               | TRUECURRENT®*                                                                               |
| ESBC™                                                                               | MicroPak2™                                                                          | SPM®                                                                                       | µSerDes™                                                                                    |
|  ® | MillerDrive™                                                                        | STEALTH™                                                                                   |  SerDes™ |
| Fairchild®                                                                          | MotionMax™                                                                          | SuperFET®                                                                                  | UHC®                                                                                        |
| Fairchild Semiconductor®                                                            | Motion-SPM™                                                                         | SuperSOT™-3                                                                                | Ultra FRFET™                                                                                |
| FACT Quiet Series™                                                                  | mWSaver™                                                                            | SuperSOT™-6                                                                                | UniFET™                                                                                     |
| FACT®                                                                               | OptiHiT™                                                                            | SupersOT™-8                                                                                | VCX™                                                                                        |
| FAST®                                                                               | OPTOLOGIC®                                                                          | SupreMOS®                                                                                  | VisualMax™                                                                                  |
| FastvCore™                                                                          | OPTOPLANAR®                                                                         | SyncFET™                                                                                   | XS™                                                                                         |
| FETBench™                                                                           |  ® | Sync-Lock™                                                                                 |                                                                                             |
| FlashWriter® *                                                                      | PDP SPM™                                                                            |  SYSTEM®* |                                                                                             |

\*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status        | Definition                                                                                                                                                                                          |
|--------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production      | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production       | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.                                               |
| Obsolete                 | Not In Production     | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.                                                    |

Rev. I54

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada

**Europe, Middle East and Africa Technical Support:**  
Phone: 421 33 790 2910

**Japan Customer Focus Center**  
Phone: 81-3-5817-1050

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)

**Order Literature:** <http://www.onsemi.com/orderlit>

For additional information, please contact your local  
Sales Representative