

KEMET Part Number: C0805C103J3GACTU
(C0805C103J3GAC7800)

Ceramic, Commercial-(CxxxxC), 0.01 uF, 5%, 25 V, 0805, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I



General Information	
Style:	SMD Chip
Series:	Commercial-(CxxxxC)
Chip Size:	0805
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Features:	Ultra-Stable, Low Loss, Class I
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A

Dimensions	
L	2mm +/-0.2mm
W	1.25mm +/-0.2mm
T	0.78mm +/-0.10mm
S	0.75mm MIN
B	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

Specifications	
Capacitance:	0.01 uF
Capacitance Tolerance:	5%
Voltage DC:	25 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	C0G
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms
Dielectric Strength:	62.5 V