

**KEMET Part Number: C1206C106Z8VACTU**  
(C1206C106Z8VAC7800)

Ceramic, Commercial-(CxxxxC), 10 uF, -20/+80%, 10 V, 1206, Y5V, SMD, MLCC, General Purpose, Class III



**Dimensions**

|          |                 |
|----------|-----------------|
| <b>L</b> | 3.2mm +/-0.2mm  |
| <b>W</b> | 1.6mm +/-0.2mm  |
| <b>T</b> | 1.6mm +/-0.20mm |
| <b>B</b> | 0.5mm +/-0.25mm |

**Packaging Specifications**

|                            |                          |
|----------------------------|--------------------------|
| <b>Packaging:</b>          | T&R, 180mm, Plastic Tape |
| <b>Packaging Quantity:</b> | 2000                     |

**General Information**

|                       |  |
|-----------------------|--|
| <b>Style:</b>         | SMD Chip   |
| <b>Series:</b>        | Commercial-(CxxxxC)  |
| <b>Chip Size:</b>     | 1206   |
| <b>Description:</b>   | SMD, MLCC, General Purpose, Class III                                  |
| <b>Features:</b>      | Class III  |
| <b>RoHS:</b>          | Yes  |
| <b>Termination:</b>   | Tin  |
| <b>Marking:</b>       | No   |
| <b>Failure Rate:</b>  | N/A  |
| <b>Miscellaneous:</b> | Note: Referee time for Y5V dielectric for this part number is 48 hours |

**Specifications**

|                                 |                     |
|---------------------------------|---------------------|
| <b>Capacitance:</b>             | 10 uF               |
| <b>Capacitance Tolerance:</b>   | -20/+80%            |
| <b>Voltage DC:</b>              | 10 VDC              |
| <b>Temperature Range:</b>       | -30/+85C            |
| <b>Temperature Coefficient:</b> | Y5V                 |
| <b>Dissipation Factor:</b>      | 10%                 |
| <b>Aging Rate:</b>              | 7% Loss/Decade Hour |
| <b>Insulation Resistance:</b>   | 5 MOhms             |
| <b>Dielectric Strength:</b>     | 25 V                |