










Model Number

NBN8-18GM60-WS

Features

- 8 mm not embeddable
- 2-wire AC

Connection




Accessories

BF 18

Mounting flange, 18 mm

Dimensions



Technical Data General specifications

	Switching element function		AC	NO
	Rated operating distance	s _n	8 mm	
	Installation		not embed	Idable
	Output polarity		AC	
	Assured operating distance	sa	0 6.48 m	mm
	Reduction factor r _{Al}		0.4	
	Reduction factor r _{Cu}		0.4	
	Reduction factor r ₃₀₃		0.7	
Nominal ratings				
	Operating voltage	U _B	20 253 \	V
	Switching frequency	f	0 20 Hz	
	Hysteresis	Н	typ. 7.5 %	
	Reverse polarity protected		tolerant	
	Voltage drop	U _d	< 5 V (I _L >	50 mA); < 8 V (I _L < 50 mA)
	Momentary current		0 1600 n	mA
	(20 ms, 0.1 Hz)			
	Operating current	I _L	5 200 m	
	Off-state current	l _r	0 1.7 mA	
	Operating voltage display		LED, greer	
	Indication of the switching state		I FD vellov	W.

Ambient conditions

Ambient temperature -25 ... 70 °C (-13 ... 158 °F)

Mechanical specifications

cable PVC , 2 m $0.34~\text{mm}^2$ Connection type Core cross-section Housing material Sensing face brass, nickel-plated 1) In the temperature range below 0 °C, permissible operating voltage U_b 80...253 V Safety fuse \leq 0.8 A (quick-blow) according to IEC 60127-2 Sheet 1 Protection degree Note

Recommendation: after a short circuit, check that the device is functioning correctly.

Compliance with standards and directives

Standard conformity EN 60947-5-2:2007 Standards IEC 60947-5-2:2007

Approvals and certificates

cULus Listed, General Purpose UL approval CSA approval cCSAus Listed, General Purpose CCC approval Certified by China Compulsory Certification (CCC)