

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1712244011](#)
Status: **Active**
Overview: [High-Speed Pluggable I/O Solutions](#)
Description: zSFP+® Stacked Ganged Assembly with Metal Spring Fingers, 2-by-4 with 4 Light Pipes, 160 Circuits

Documents:

3D Model	Packaging Specification PK-170071-001 (PDF)
Drawing (PDF)	Packaging Specification PK-170071-002 (PDF)
Product Specification PS-170071-0001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-170071-0002 (PDF)	

Agency Certification

UL E29179

General


Product Family	I/O Connectors
Series	171224
Application	Module-to-Board
Component Type	Receptacle
Overview	High-Speed Pluggable I/O Solutions
Product Name	zSFP+®
Type	N/A
UPC	884982823617

Physical

Circuits (Loaded)	160
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	97.386/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 0.5A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[171224](#) Series

Shield Type	N/A
Shielded	Yes
Voltage - Maximum	30V AC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-170071-0002
Packaging Specification	PK-170071-001, PK-170071-002
Product Specification	PS-170071-0001
Sales Drawing	SD-171224-0002

This document was generated on 06/10/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION