

KEMET Part Number: C1210C224J3GACTU
(C1210C224J3GAC7800)

Ceramic, Commercial-(CxxxxC), 0.22 uF, 5%, 25 V, 1210, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I



| General Information | |
|---------------------|--|
| Style: | SMD Chip |
| Series: | Commercial-(CxxxxC) |
| Chip Size: | 1210 |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |

| Dimensions | |
|------------|-----------------|
| L | 3.2mm +/-0.2mm |
| W | 2.5mm +/-0.2mm |
| T | 2.1mm +/-0.20mm |
| B | 0.5mm +/-0.25mm |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2000 |

| Specifications | |
|--------------------------|---------------------|
| Capacitance: | 0.22 uF |
| Capacitance Tolerance: | 5% |
| Voltage DC: | 25 VDC |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | C0G |
| Dissipation Factor: | 0.1% |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 4.545 GOhms |
| Dielectric Strength: | 62.5 V |