

**KEMET Part Number: PHE850EB5470MB14R17**  
(F850BV473M300A)



Film, Metallized Polypropylene, Safety, PHE850/F850, 0.047 uF, 20%, 1,250 V, 300 V, 110C, Lead Spacing = 15mm



General Information	
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Series:</b>	PHE850/F850
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Approvals:</b>	ENEC, UL, cUL
<b>Miscellaneous:</b>	Not For New Design, Please Check Possible Alternative Parts (AltPart)

Dimensions	
<b>L</b>	18mm MAX
<b>H</b>	17.5mm MAX
<b>T</b>	9.5mm MAX
<b>S</b>	15mm +/-0.4mm
<b>LL</b>	17mm NOM
<b>F</b>	0.8mm NOM

Specifications	
<b>Capacitance:</b>	0.047 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	1250 VDC
<b>Voltage AC:</b>	300 VAC
<b>Temperature Range:</b>	-55/+110C
<b>Rated Temperature:</b>	110C
<b>Dissipation Factor:</b>	0.15% 1kHz, 0.2% 10kHz, 0.6% 100kHz
<b>Insulation Resistance:</b>	30 GOhms
<b>Max dVdt:</b>	100 V
<b>Safety Class:</b>	Y2

Packaging Specifications	
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	300

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2017 IntelliData.net