



Drawings not to scale
All dimensions in mm (inches) nominal
UL Approved

SPECIFICATION

CONTACT FORM/STYLE		Normally Closed
SWITCHING VOLTAGE	Max. Vac RMS	240
SWITCHING CURRENT	Max. A	12.5 at 120Vac
SWITCHING CAPACITY	Max. VA	1500W
ENCAPSULATED		YES
OPERATING ANGLE	Max. Deg. °	35 ± 10
CONTACT RESISTANCE	Max. Ω	5
OPERATING TEMPERATURE	Deg. °C	-20° +70°
STORAGE TEMPERATURE	Deg. °C	-25° +70°
CASE MATERIAL		Polypropylene
CABLE/TERMINATION		2 X 17 AWG Round silicone rubber insulated

TILT/TIP SWITCH ASSEMBLIES

PART NUMBER
S1116

Rev. No.	Revision Note	Date	Signature
C	Web Site 1999	1-6-99	RG

The Comus Group of Companies
consist of:
Assemtech Europe Limited
E. Bachem GmbH
Comus International
W. Gunther GmbH
Gunther Belgium
Gunther France
S.T.G.

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.